



Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: **Plug**
Connector System: **Wire-to-Board**
Number of Positions: **2**
Centerline (Pitch): **5 mm [.197 in]**
Number of Rows: **1**

Features

Product Type Features

Wire Protection	With
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Wire Entry Location	Side
Stacking Configuration	Side Stackable
Number of Positions	2
Number of Rows	1
Wire Entry Angle	180°

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Black
-----------------------	-------



Product Orientation	Right Angle
Contact Features	
Contact Mating Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	15 A
Mechanical Attachment	
Screw Plating Material	Nickel
Screw Material	Brass
Thread Size	M3
Connector Mounting Type	Board Mount
Housing Features	
Housing Material	PA 66
Centerline (Pitch)	5 mm[.197 in]
Dimensions	
Wire Size	.05 – 3 mm²
Usage Conditions	
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
Operation/Application	
Circuit Application	Power & Signal
Packaging Features	
Packaging Quantity	200
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (.63% in Component Part)






Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 796644-2 2POS 5.0MM CE R/A HDR,TRM BLK	 TE Part # 796642-2 2POS 5.0MM CE VRT HDR,TRM BLK	 TE Part # 282822-2 TERMI-BLOK HEADER,ASSY90 2P.	 TE Part # 1776138-2 2P TERMI-BLOK HDR,HIGH TEMP
 TE Part # 1776146-2 2P TERMI-BLOK HDR,HIGH TEMP	 TE Part # 282812-2 TERMI-BLOK HEADER,ASSY 2P. 5	 TE Part # 796645-2 2POS 5.0MM CE R/A HDR,TRM BLK	 TE Part # 1776166-2 2P TERMI-BLOK HDR,HIGH TEMP
 TE Part # 1776164-2 2P TERMI-BLOK HDR,HIGH TEMP	 TE Part # 796643-2 2POS 5.0MM CE VRT HDR,TRM BLK		



Customers Also Bought



TE Part #5050935-2
SOCKET,MIN-SPR SN-SN SER-1




TE Part #35664
TERMINAL,SOLIS R 8 1/2




TE Part #DTP4S-BT
BOOT, 4P, PLG, ST, GRY



TE Part #770022-1
12P UMNLI IN-LNE PLUG HSG KIT



TE Part #1-640517-0
02P MR II PLUG HSG



TE Part #796642-2
2POS 5.0MM CE VRT HDR,TRM BLK



TE Part #2176331-2
CRGP 2512 12R 1%



TE Part #1813271-1
SEALED MT2 PLUG HOUSING ASSEMBLY



TE Part #NB17932001
RNF-100-1-1/2-BK-STK



TE Part #474818-E
SRCP 1,27 8 M 1-KS SMD 137 E1 094 * GU-H

Documents

Product Drawings
2 POS 5.0 MM R/A PLUG,TRM BLK
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_796641-2_E.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_796641-2_E.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_796641-2_E.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English