


FLKM-2FLK14/FKDSP-MT/DIL/HF/S7 - Passive module



2296883
<https://www.phoenixcontact.com/us/products/2296883>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE termination board for Siemens SIMATIC® S7-300, with SIMATIC®-specific marking (1 - 20) and additional 18 connection terminal blocks (positive potential). Several terminal points can be bridged via one switch.

Commercial data

Item number	2296883
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	CK218S
GTIN	4017918729448
Weight per piece (including packing)	234.2 g
Weight per piece (excluding packing)	231.1 g
Customs tariff number	85369010
Country of origin	DE

FLKM-2FLK14/FKDSP-MT/DIL/HF/S7 - Passive module



2296883

<https://www.phoenixcontact.com/us/products/2296883>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Operating mode	100% operating factor

Data management status

Article revision	07
------------------	----

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 30 V DC
Current (per branch)	≤ 1 A
Current (Voltage supply)	≤ 3 A

Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 µs)

Supported controller SIEMENS S7-300 / ET 200 M

Suitable I/O card	6ES7331-7KF02-0AB0
-------------------	--------------------

Connection data

Connection 1 (control level)

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK pin strip
Number of connections	2
Number of positions	14
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Connection 2 (field level)

Connection method	Push-in spring connection
Stripping length	10 mm
Number of connections	1
Number of positions	18
Conductor cross section rigid	0.2 mm² ... 1.5 mm²
Conductor cross section flexible	0.2 mm² ... 1.5 mm² 0.25 mm² ... 1.5 mm² (Ferrule without plastic sleeve)

FLKM-2FLK14/FKDSP-MT/DIL/HF/S7 - Passive module



2296883

<https://www.phoenixcontact.com/us/products/2296883>

	0.25 mm² ... 1.5 mm² (Ferrule with plastic sleeve)
Conductor cross section AWG	24 ... 16
Pitch	5.08 mm

Connection 3 (field level)

Connection method	PCB terminal block
Type	PCB isolating plugs
Number of connections	1
Number of positions	18
Pitch	5.08 mm

Connection 4 (supply)

Connection method	Push-in spring connection
Number of connections	2
Number of positions	2
Conductor cross section rigid	0.2 mm² ... 1.5 mm²
Conductor cross section flexible	0.2 mm² ... 1.5 mm²
	0.25 mm² ... 1.5 mm² (Ferrule without plastic sleeve)
	0.25 mm² ... 1.5 mm² (Ferrule with plastic sleeve)
Conductor cross section AWG	24 ... 16
Pitch	5.08 mm

Connection 5 (supply)

Connection method	PCB terminal block
Type	PCB isolating plugs
Number of connections	2
Number of positions	2

Dimensions

Item dimensions

Width	123.5 mm
Height	77 mm
Depth	57.17 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Approvals

UKCA

FLKM-2FLK14/FKDSP-MT/DIL/HF/S7 - Passive module



2296883
<https://www.phoenixcontact.com/us/products/2296883>

Certificate	UKCA-compliant
-------------	----------------

Standards and regulations

Air clearances and creepage distances	
Standards/regulations	EN IEC 60664-1

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKM-2FLK14/FKDSP-MT/DIL/HF/S7 - Passive module



2296883
<https://www.phoenixcontact.com/us/products/2296883>

Classifications

ECLASS

ECLASS-11.0	27141152
ECLASS-12.0	27141152
ECLASS-13.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FLKM-2FLK14/FKDSP-MT/DIL/HF/S7 - Passive module



2296883
<https://www.phoenixcontact.com/us/products/2296883>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com