



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Hood**

Cable Entry Location: **Side**

Features

Product Type Features

Hood & Base Connector Product Type	Hood
------------------------------------	------

Body Features

Primary Product Color	Gray
Cable Entry Location	Side

Mechanical Attachment

Locking Device Location	Housing
Thread Size	M25

Housing Features

Housing Material	Die Cast Aluminum
------------------	-------------------

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Packaging Features

Packaging Quantity	1
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # T3609250102-000 DLX-25-M	 TE Part # T1319320125-000 H32A-TS-M25	 TE Part # T2010322201-000 HA-016-F 17-32	 TE Part # T2010162201-000 HA-016-F
---	---	---	---

Also in the Series | HDC IP65


 Rectangular Connector Hoods & Bases (1258)

Customers Also Bought





TE Part #T2010102201-000
HA-010-F




TE Part #T2020642101-000
HD-064-M



TE Part #T1449320225-000
H32A-SGR-2M25



TE Part #T2010322101-000
HA-016-M 17-32



TE Part #T2020252201-000
HD-025-F



TE Part #1-2071567-2
ECK200AAAPA



TE Part #T1230240132-000
H24B-TSH-M32



TE Part #T2010162201-000
HA-016-F



TE Part #T2030002002-000
CEF-0.3



TE Part #T3209321222-001
HSK-M32G

Documents

Product Drawings
H32A-SGR-M25

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_T1449320125-000_A.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_T1449320125-000_A.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_T1449320125-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Product Specifications

Application Specification

English

Application Specification