




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **2050 – 5180 CMA**

Mating Tab Width: **2.79 mm [.11 in]**

Features

Product Type Features

Terminal Features	Wire Stop
Insertion Force	Low

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Body Features

Insulation Material	Nylon
---------------------	-------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	2.79 mm[.11 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Pre-Tin
Crimp Type	Compression
Barrel Type	Closed

Termination Features



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Terminal Material Thickness	.41 mm[.016 in]
Product Length	20.36 mm[.8 in]
Compatible Insulation Diameter Range	4.32 mm[.17 in]
Wire Size	2050 – 5180 CMA

Usage Conditions

Insulation Option	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, RU (UL Component Program)
---	--------------------------------

Packaging Features

Packaging Quantity	100
Packaging Method	Loose Piece

Other

Barrel Color	Blue
--------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 640929-1
RECEPT,PIDG FASTON 16-14 110

TE Part # 640929-2
RECEPT,PIDG FASTON 16-14 110

TE Part # 1SET162030R0000

Also in the Series | FASTON 110

Crimp Terminal Housings(13)

Insertion & Extraction Tools(1)

PCB Terminals(22)

Quick Disconnects(168)

Customers Also Bought

TE Part #52930
PIDG SP SPD 22-16COMM22-18MIL8

TE Part #T4073014031-001
M8.FMLE.PNLFRONT.3POS.STR WIRE

TE Part #1-2199298-8
24P,DIP SKT,300 CL,LDR,PB FREE


TE Part #2-520084-2
ULTRAFast 110 ASSY REC 22-18 TPBR LP





TE Part #5-520315-7

TRIOMATE ASSY V 7P L=3.556



TE Part #5-534998-6

12 MODIV VRT DR CE 100/125




TE Part #130014

TERM, R, PG, 22-16, M5



TE Part #54775-1

TERMINAL,PG R 16-14 6-8-10



TE Part #1487598-1

USB, A-B, 25/20, BLACK, 4.0M

Documents

Product Drawings

RECEPT,PIDG FASTON 16-14 110

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_8-640929-1_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_8-640929-1_G.3d_igs.zip

English

Customer View Model

ENG_CVM_8-640929-1_G.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-640929-1_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_8-640929-1_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-640929-1_F.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English