

CUC-IND-C1ZNI-S/R4IE10G8 - RJ45 connector



1149846
<https://www.phoenixcontact.com/us/products/1149846>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6_A, material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 26- 24, cable outlet: straight, color: yellow, Ethernet

Your advantages

- Easy and time-saving assembly with IDC fast connection technology
- Can be used internationally due to EAC, UL 1863, and CAN/CSA C22.2
- Ideal companion for servicing or repairs in the field: no special tools required for mounting
- 360° shielding ensures reliable transmission, even in industrial applications
- Ideal for demanding applications due to the high shock and vibration resistance as well as the extended temperature range
- Innovative one-piece design prevents mounting errors and the loss of small parts
- Future-proof due to CAT6_A with 10 Gbps

Commercial data

Item number	1149846
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB10
Product key	ABNAAB
GTIN	4063151146320
Weight per piece (including packing)	18.1 g
Weight per piece (excluding packing)	15.8 g
Customs tariff number	85366990
Country of origin	PL

CUC-IND-C1ZNI-S/R4IE10G8 - RJ45 connector



1149846

<https://www.phoenixcontact.com/us/products/1149846>

Technical data

Product properties

Product type	Data connector (cable side)
Type	RJ45
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Type	RJ45
Shielded	yes
Cable outlet	straight
Positions/contacts	8P8C

Data management status

Article revision	02
------------------	----

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Contact resistance	< 20 mΩ (Contact)
	< 100 mΩ (shield)
Frequency range	500 Hz
Insulation resistance	> 500 MΩ
Contact resistance per contact pair	< 20 Ω
Contact resistance	> 10 mΩ (Wire – IDC)
	0.005 Ω (Litz wires – IDC)
Transmission characteristics (category)	CAT6 _A
Transmission speed	10 Gbps
Power transmission	PoE++
Wave impedance	100 Ω

Connection data

Connection technology

Connection method	Insulation displacement connection
Connection cross section AWG	26 ... 24 (solid)
	26 ... 24 (flexible)
Conductor cross section	0.14 mm² ... 0.22 mm² (solid)
	0.14 mm² ... 0.22 mm² (flexible)
Connection in acc. with standard	IEC 60603-7-51

CUC-IND-C1ZNI-S/R4IE10G8 - RJ45 connector



1149846

<https://www.phoenixcontact.com/us/products/1149846>

Cable outlet, angle	180
---------------------	-----

Dimensions

Width	13.65 mm
Height	14.4 mm
Length	53 mm

Material specifications

Color	yellow
Material	Plastic
Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	Ni
Cable seal material	NBR
Contact material	CuSn
Contact surface material	Au/Ni
Contact carrier material	PC
Locking latch material	Stainless steel
Material for screw connection	PA

Cable/line

External cable diameter	5 mm ... 9 mm
Wire diameter including insulation	≤ 1.6 mm
Cable cross section	0.14 mm ²
Test voltage Core/Core	1000 V
Test voltage Core/Shield	1500.00 V
Wave impedance	100 Ω

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 750
-----------------------------	-------

Environmental and real-life conditions

Test specification

Type of test	Vibration test
Specification	IEC 60068-2-6
Frequency	2-2000 Hz
Sweep speed	1 octave/min
Amplitude	1.00 mm
Acceleration	200.00 m/s ²
Test duration	20.00 s

Test specification

Type of test	Shock testing
--------------	---------------

CUC-IND-C1ZNI-S/R4IE10G8 - RJ45 connector



1149846

<https://www.phoenixcontact.com/us/products/1149846>

Specification	IEC 60068-2-27
Acceleration	491.00 m/s²
Number of shocks per direction	5.00

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

Mounting

Mounting type	For field assembly
---------------	--------------------

CUC-IND-C1ZNI-S/R4IE10G8 - RJ45 connector




1149846

<https://www.phoenixcontact.com/us/products/1149846>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1149846>

<div> cULus Recognized Approval ID: E335024-20170228</div>				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	56.5 V	0.175 A	-	-

CUC-IND-C1ZNI-S/R4IE10G8 - RJ45 connector



1149846

<https://www.phoenixcontact.com/us/products/1149846>

Classifications

ECLASS

ECLASS-11.0	27440101
ECLASS-12.0	27440113
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-IND-C1ZNI-S/R4IE10G8 - RJ45 connector



1149846
<https://www.phoenixcontact.com/us/products/1149846>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com