




Terminals & Splices > Splices > COPALUM Stranded/Solid: Butt Splices



Splice Type: **Butt Splice**

Wire Size: **5 mm²**

Sealable: **No**

Compatible Insulation Diameter Range: **5.82 mm [.207 in]**

[All COPALUM Stranded/Solid: Butt Splices \(9\)](#)

Features

Product Type Features

Splice Accessory Type	Splice
Splice Type	Butt Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Stranded

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Product Weight	9.757 g
----------------	---------

Contact Features

Terminal Plating Material	Tin
Contact Base Material	Copper
Barrel Type	Open

Dimensions

Wire Size	5180 – 13100 CMA
Compatible Insulation Diameter Range	5.82 mm[.207 in]
Terminal Material Thickness	1.58 mm[.062 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]
-----------------------------	----------------------------

Operation/Application

Compatible With Wire Base Material	Aluminum, Copper
------------------------------------	------------------

Packaging Features

Packaging Quantity	40000
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings
SPLICE,COPALUM BUTT 8 12-10
English

CAD Files
Customer View Model
ENG_CVM_51826_D.3d_igs.zip
English
Customer View Model
ENG_CVM_51826_D.3d_stp.zip
English
Customer View Model
ENG_CVM_51826_D.2d_dxf.zip
English
3D PDF
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
COPALUM Lite Sealed Terminals and Splices
English

Product Specifications
Application Specification
English
COPALUM Terminals And Splices For Solid And Stranded Wire

English

Application Specification

Japanese

Copalum Terminals & Splices f/Solid & Stranded Wire

Japanese

Agency Approvals

UL Report

English

UL Report

English