

62627-1 ✓ ACTIVE

FASTON | FASTON 250

TE Internal #: 62627-1

Tab, Mating Tab Width 6.35 mm [.25 in], PCB Hole Diameter 3.68 mm [.145 in], Through Hole - Screw, Tin Plating, None, Bag, FASTON 250, PCB Terminals

[View on TE.com >](#)



Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

PCB Hole Diameter: **3.68 mm [.145 in]**

Termination Method to PCB: **Through Hole - Screw**

Features

Product Type Features

Terminal Features	Stud Hole
Insertion Force	Normal

Contact Features

Terminal Plating Finish	Matte
PCB Contact Termination Area Plating Material Thickness	2.03 – 3.81 μ m[80 – 150 μ in]
Contact Mating Area Plating Material Thickness	2.03 – 3.81 μ m[80 – 150 μ in]
PCB Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Plating Material	Tin
Contact Underplating Material	None
Terminal Size	6.35
Terminal Orientation	Straight

Termination Features



Termination Method to PCB	Through Hole - Screw
---------------------------	----------------------

Product Terminates To	Printed Circuit Board
-----------------------	-----------------------

Dimensions

Stud Diameter	3.68 mm [.145 in]
---------------	-------------------

PCB Hole Diameter	3.68 mm [.145 in]
-------------------	-------------------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

Packaging Features

Packaging Quantity	1000
--------------------	------

Packaging Method	Bag
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 63038-1
250 FASTON TAB TPBR



TE Part # 61499-1
250 FASTON TAB TPBR



TE Part # 61365-1
250 FASTON TAB TPBR



TE Part # 62627-2
250 FASTON TAB BR



TE Part # 60920-5
187 FASTON TAB TPBR



TE Part # 60922-5
FASTON .205 SERIES (5.2 MM) TAB TPST



TE Part # 60920-1
187 FASTON TAB BR



TE Part # 1217002-1
250 FASTON, TAB, NPCST



TE Part # 63971-1
250 FASTON TAB TPBR



TE Part # 62627-3
250 FASTON TAB BR



TE Part # 140736-2
250 FASTON, TAB, TPBR



TE Part # 60921-1
205 FASTON SERIES TAB BR




TE Part # 60922-1
205 FASTON SERIES TAB BR




TE Part # 63274-3
250 FASTON TAB BR


Also in the Series | FASTON 250




Compression Connectors(4)



Crimp Terminal Housings(132)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(134)



Quick Disconnects(426)



Splices(4)

Customers Also Bought



TE Part #T4171110005-001
M12,REAR MOUNTING,FEMALE,A,5P,
0.2M WIRE



TE Part #5-2176230-1
3522 12K 5% 3W



TE Part #T4145015041-001
M12 Panel Mount PCB



TE Part #5650868-4
ASSY,RECEPTACLE,EUROCARD,TYPE



TE Part #2-1445096-5
MICRO MNL HDR ASSY SINGLE ROW



TE Part #641971-1
09P UMNL PIN HDR ASSY V2 NATL



TE Part #641969-1
06P UMNL PIN HDR ASSY V2 NATL



TE Part #641967-1
04P UMNL PIN HDR ASSY POL NATL



TE Part #644178-1
07P MTA100 HDR ASSY W/O#5

Documents

Product Drawings

[250 FASTON TAB TPST](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_62627-1_P.2d_dxf.zip](#)

62627-1

Tab, Mating Tab Width 6.35 mm [.25 in], PCB Hole Diameter 3.68 mm [.145 in],
Through Hole - Screw, Tin Plating, None, Bag, FASTON 250, PCB Terminals



English

Customer View Model

[ENG_CVM_CVM_62627-1_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_62627-1_P.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTON Tabs

English