


Automotive N-Channel 100 V (D-S) 175 °C MOSFET


PowerPAK® 8 x 8LR


FEATURES

- TrenchFET® Gen IV power MOSFET
- AEC-Q101 qualified
- 100 % R_g and UIS tested
- Thin 1.9 mm height
- Material categorization:
for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE



N-Channel MOSFET

PRODUCT SUMMARY

V_{DS} (V)	100
$R_{DS(on)}$ (Ω) at $V_{GS} = 10$ V	0.00253
I_D (A)	296
Configuration	Single

ORDERING INFORMATION

Package	PowerPAK 8 x 8LR
Lead (Pb)-free and halogen-free	SQJQ112ER (for detailed order number please see www.vishay.com/doc?79776)

ABSOLUTE MAXIMUM RATINGS ($T_C = 25$ °C, unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNIT
Drain-source voltage	V_{DS}	100	V
Gate-source voltage	V_{GS}	± 20	V
Continuous drain current	I_D	296	A
$T_C = 25$ °C		171	
Continuous source current (diode conduction)	I_S	545	
Pulsed drain current ^a	I_{DM}	655	
Single pulse avalanche current	I_{AS}	69	mJ
Single pulse avalanche energy	E_{AS}	242	
Maximum power dissipation	P_D	600	W
		200	
Operating junction and storage temperature range	T_J, T_{stg}	-55 to +175	°C
Soldering recommendations (peak temperature) ^c		260	

THERMAL RESISTANCE RATINGS

PARAMETER	SYMBOL	LIMIT	UNIT
Junction-to-ambient	R_{thJA}	40	°C/W
Junction-to-case (drain)	R_{thJC}	0.25	

Notes

- a. Pulse test; pulse width ≤ 300 μ s, duty cycle ≤ 2 %
b. When mounted on 1" square PCB (FR4 material)
c. See solder profile (www.vishay.com/doc?73257)



SPECIFICATIONS (T _C = 25 °C, unless otherwise noted)							
PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT
Static							
Drain-source breakdown voltage	V _{DS}	V _{GS} = 0, I _D = 250 μA		100	-	-	V
Gate-source threshold voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA		2	3	3.5	
Gate-source leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 20 V		-	-	± 100	nA
Zero gate voltage drain current	I _{DSS}	V _{GS} = 0 V	V _{DS} = 100 V	-	-	1	μA
		V _{GS} = 0 V	V _{DS} = 100 V, T _J = 125 °C	-	-	50	
		V _{GS} = 0 V	V _{DS} = 100 V, T _J = 175 °C	-	-	500	
On-state drain current ^a	I _{D(on)}	V _{GS} = 10 V	V _{DS} ≥ 5 V	50	-	-	A
Drain-source on-state resistance ^a	R _{DS(on)}	V _{GS} = 10 V	I _D = 20 A	-	0.0021	0.00253	Ω
		V _{GS} = 10 V	I _D = 20 A, T _J = 125 °C	-	-	0.0054	
		V _{GS} = 10 V	I _D = 20 A, T _J = 175 °C	-	-	0.0068	
Forward transconductance ^b	g _{fs}	V _{DS} = 15 V, I _D = 15 A		-	45	-	S
Dynamic ^b							
Input capacitance	C _{iss}	V _{GS} = 0 V	V _{DS} = 25 V, f = 1 MHz	-	11388	15 945	pF
Output capacitance	C _{oss}			-	1326	1857	
Reverse transfer capacitance	C _{rss}			-	80	112	
Total gate charge ^c	Q _g	V _{GS} = 10 V	V _{DS} = 50 V, I _D = 20 A	-	181	272	nC
Gate-source charge ^c	Q _{gs}			-	48	-	
Gate-drain charge ^c	Q _{gd}			-	37	-	
Gate resistance	R _g	f = 1 MHz		0.7	1.5	2.3	Ω
Turn-on delay time ^c	t _{d(on)}	V _{DD} = 50 V, R _L = 2.5 Ω, I _D ≅ 20 A, V _{GEN} = 10 V, R _g = 1 Ω		-	21	30	ns
Rise time ^c	t _r			-	16	24	
Turn-off delay time ^c	t _{d(off)}			-	67	95	
Fall time ^c	t _f			-	16	24	
Source-Drain Diode Ratings and Characteristics ^b							
Pulsed current ^a	I _{SM}			-	-	655	A
Forward voltage	V _{SD}	I _F = 40 A, V _{GS} = 0 V		-	0.7	1.2	V
Body diode reverse recovery time	t _{rr}	I _F = 15 A, di/dt = 100 A/μs		-	70	140	ns
Body diode reverse recovery charge	Q _{rr}			-	172	344	nC
Reverse recovery fall time	t _a			-	44	-	ns
Reverse recovery rise time	t _b			-	26	-	
Body diode peak reverse recovery current	I _{RM(REC)}			-	4.3	-	A


Notes

- a. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$
b. Guaranteed by design, not subject to production testing
c. Independent of operating temperature


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




TYPICAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$, unless otherwise noted)




Output Characteristics




Transfer Characteristics




Transconductance









On-Resistance vs. Drain Current



Capacitance




Gate Charge

TYPICAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$, unless otherwise noted)

On-Resistance vs. Junction Temperature

Source Drain Diode Forward Voltage

Drain Source Breakdown vs. Junction Temperature

On-Resistance vs. Gate-to-Source Voltage

Threshold Voltage

Safe Operating Area
Note


- $V_{GS} >$ minimum V_{GS} at which $R_{DS(on)}$ is specified



THERMAL RATINGS ($T_A = 25\text{ }^{\circ}\text{C}$, unless otherwise noted)




Normalized Thermal Transient Impedance, Junction-to-Case



Normalized Thermal Transient Impedance, Junction-to-Ambient

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?66837.

Recommended Land Pattern PowerPAK® 8 x 8LR



Notes

- This land pattern is for reference
- Proposed stencil thickness 200 µm
- All dimensions are in millimeter (inches)

ECN: C23-0461-Rev. B, 17-Apr-2023

DWG: 3002



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.