

HDP24-24-29SE-L017

✓ ACTIVE

DEUTSCH | [DEUTSCH HD](#), [DEUTSCH HDP](#)

TE Internal #: HDP24-24-29SE-L017

Housing for Female Terminals, Wire-to-Panel, 29 Position, Sealable, Black, Wire & Cable, Power, Panel Mount, -55 – 125 °C [-67 – 257 ° F], Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH HDP20 Housings



Connector System: **Wire-to-Panel**
Number of Positions: **29**
Connector & Housing Type: **Housing for Female Terminals**
Sealable: **Yes**
Mating Pin Diameter: **1 mm, 1.6 mm, 2.4 mm [.04 in, .063 in, .094 in]**

[All DEUTSCH HDP20 Housings \(357\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	Yes
Connector Shape	Circular
Connector System	Wire-to-Panel
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Contact Retainer

Configuration Features

Blank Cavity Position	0
Connector Modification	Ring Adapter
Connector Seal Code	E Seal
Number of Positions	29

Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	250 V

Body Features



Cable Exit Angle	180°
Primary Product Color	Black

Contact Features

Contact Size	Size 12, Size 16, Size 20
Contact Type	Socket
Mating Pin Diameter	1 mm, 1.6 mm, 2.4 mm[.04 in][.063 in][.094 in]
Contact Current Rating (Max)	7.5 A, 13 A, 25 A

Mechanical Attachment

Terminal Position Assurance	No
Strain Relief	Without
Mating Alignment Type	Polarization Slot
Mating Alignment	With
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	PA 66 GF
------------------	----------

Dimensions

Connector Height	45.8 mm[1.8 in]
Product Width	47.6 mm[1.87 in]
Product Length	50.8 mm[2 in]
Compatible Insulation Diameter Range	1.4 – 3.8 mm, 1.9 – 3.2 mm, 3.6 – 5.2 mm[.055 – .15 in][.075 – .125 in][.14 – .204 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Degree of Protection	IP67
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	30
--------------------	----



Packaging Method

Tray

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D48-SP729
DEUTSCH Sealing Plugs



TE Part # CAT-H396-RC8382
Receptacle Protective Caps —
DEUTSCH HDP20



TE Part # CAT-H396-B128
DEUTSCH HDP20 Backshells



TE Part # CAT-H396-CH8172
DEUTSCH HDP20 Housings





TE Part # HD30-24BT-BK
BOOT, 24SZ, ST, BLK



TE Part # 24-D-PUNCH
D-HOLE PUNCH, SIZE 24



TE Part # 0411-337-1205
EXT TOOL, SIZE 12, 12-14 AWG, E,
ORG



TE Part # 0411-240-2005
EXT TOOL, SIZE 20, 16-22 AWG, N,
RED



TE Part # 16-04477
GASKET, 24SZ, BLK, HD30




TE Part # HD30-24BT
BOOT, 24SZ, ST, GRY



TE Part # HD30-24BT-90-BK
BOOT, 24SZ, RA, BLK




TE Part # 0411-336-1605
EXT TOOL, SIZE 16, 16-20 AWG, E,
DRK BLU




TE Part # 62036-40
62036 HDP24 FLANGE-SEAL silicone
60shore

Also in the Series


DEUTSCH HD




Automotive Connector Caps & Covers
(32)



Automotive Housings(768)




Connector Backshells(29)




Connector Seals & Cavity Plugs(10)



Connector Strain Relief(5)



Insertion & Extraction Tools(11)



Other Automotive Connector
Accessories(11)



PCB Headers & Receptacles(1)

Also in the Series

DEUTSCH HDP



Automotive Connector Caps & Covers (4)

Automotive Housings(357)

Connector Backshells(8)

Connector Seals & Cavity Plugs(1)

Insertion & Extraction Tools(11)

Other Automotive Connector Accessories(5)

Customers Also Bought

TE Part #DT04-12PC-C015
DEUTSCH DT Receptacle Connectors

TE Part #HDP24-24-21PE-L017
DEUTSCH HDP20 Housings

TE Part #330369
SPLICE,SOLIS BUTT 12-10

Documents

Product Drawings
REC, 29P, BLK, E, RNG, 12/16/20, S
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_HDP24-24-29SE-L017_B.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_HDP24-24-29SE-L017_B.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_HDP24-24-29SE-L017_B.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English