




Connectors > Connector Accessories > Connector Hardware



Hardware Accessory Function: **Mounting**

Connector Hardware Accessory Type: **Panel Mount Adapter**

Primary Product Color: **Black**

Number of Positions: **1**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Hardware Accessory Function	Mounting
Connector Hardware Accessory Type	Panel Mount Adapter

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Color	Black
-----------------------	-------

Mechanical Attachment

Thread Size	8-32 UNC-2A
-------------	-------------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	0 – 105 °C[32 – 221 °F]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #4-640441-5
15P MTA100 CONN ASSY WHT



TE Part #3-640426-7
07P MTA156 CONN ASSY 18AWG
ORA



TE Part #42864-2
RING CRIMP 12-10 AWG TPBR



TE Part #1062-14-0144
SOC, SF, SIZE 16, 14-18, AU/SN




TE Part #172096-1
MIC CAP 9P W-W W/F



TE Part #BSA085F52580235000
923 PLUG



TE Part #171892-1
9CIR MIC PLUG HSG



TE Part #170221-3
TAB WITH LANCE FOR M.I.C.

TE Part #1939636-2
5.0MM PITCH ELECTRO TAP CONN.

TE Part #POE-HP-50I
POE,HPInj,50V,50W

Documents

Product Drawings

MOUNTING ADAPTR,AMPINNERGY WTW

English

CAD Files

Customer View Model

ENG_CVM_CVM_557313-1_B1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_557313-1_B1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_557313-1_B1.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_557313-1_A.3d_igs.zip

English



Customer View Model

[ENG_CVM_557313-1_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_557313-1_A.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED](#)

English

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

Product Specifications

[Application Specification](#)

English