




Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **Natural**

Primary Product Material: **Nylon**

Number of Positions: **2**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Connector Cover Type	Strain Relief Cover
----------------------	---------------------

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Natural
Primary Product Material	Nylon

Mechanical Attachment

Strain Relief	With
---------------	------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]

Packaging Features

Packaging Quantity	1
Packaging Method	Package



Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 350787-3
02P UMNL PIN HDR ASSY 94VO LF

TE Part # 350787-1
02P UMNL PIN HDR ASSY 94VO

TE Part # 350428-4
02P UMNL PIN HDR ASSY NATL AU




TE Part # 350759-5
02P UMNL HDR ASSY PC V2 LF



 TE Part # 1-350942-0 02P UMNL HDR ASSY R/A 94VO	 TE Part # 350786-3 02P UMNL HDR ASSY AU 94VO	 TE Part # 350824-1 02P UMNL HDR ASSY PC 94VO	 TE Part # 643226-1 02P UMNL HDR ASSY R/A 94VO
 TE Part # 641964-1 02P UMNL PIN HDR ASSY POL 94VO	 TE Part # 350824-4 02P UMNL HDR ASSY PC LF	 TE Part # 350777-1 02P UMNL PLUG HSG	 TE Part # 350428-1 02P UMNL PIN HDR ASSY NATL
 TE Part # 350759-4 02P UMNL HDR ASSY PC V2 NATL	 TE Part # 641963-1 02P UMNL PIN HDR ASSY POL NATL	 TE Part # 641964-3 02P UMNL PIN HDR ASSY POL LF	 TE Part # 350786-1 02P UMNL HDR ASSY 94VO
 TE Part # 350778-1 02P UMNL CAP HSG	 TE Part # 1-480699-0 02P UMNL CAP HSG NATL	 TE Part # 1-480698-0 02P UMNL PLUG HSG NATL	 TE Part # 643412-1 02P UMNL HDR ASSY POL 94VO

Also in the Series

Universal MATE-N-LOK

 Circular Power Connectors(2)	 Connector Caps & Covers(34)	 Connector Contacts(209)	 Connector Hardware(12)
---	---	--	---



Connector Seals & Cavity Plugs(27)

Connector Strain Relief(7)

Insertion & Extraction Tools(4)

Rectangular Connector Housings(1)

Rectangular Power Connectors(670)

Standard Circular Connectors(1)

Customers Also Bought

TE Part #66099-3
III+ PIN,18-16,15AU/FL,LP

TE Part #640718-1
15P UMNL STR/REL

TE Part #5555141-1
MJ,LPF,R/A,8P/8C,SHLD,PNL GRD

TE Part #643030-1
05P UMNL STR/REL

TE Part #350778-1
02P UMNL CAP HSG

TE Part #160533-2
110 FASTON,REC.,20-17 AWG,TPBR

TE Part #643182-1
UMNL STR/REL ADAPTER CAP NATL

TE Part #1337773-4
50/OHM COAX BNC ELB PLUG ELB P

TE Part #1-1102101-7
HA.3.STO.1.11.Z

Documents



Product Drawings

02P UMNL STR/REL & INSERT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_640713-1_AB_c-640713-1-ab.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_640713-1_AB_c-640713-1-ab.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_640713-1_AB_c-640713-1-ab.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English