



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH DT Plug Connectors



Connector System: **Wire-to-Wire**
Number of Positions: **12**
Connector & Housing Type: **Housing for Female Terminals**
Centerline (Pitch): **4.44 mm [.175 in]**
Sealable: **Yes**

[All DEUTSCH DT Plug Connectors \(220\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Blank Cavity Position	0
Connector Modification	Shrink Boot Adapter
Connector Seal Code	E Seal
Number of Positions	12
Number of Rows	2



Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	250 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Gray
Connector & Keying Code	A

Contact Features

Contact Size	Size 16
Contact Type	Socket
Mating Pin Diameter	1.59 mm[.063 in]
Contact Current Rating (Max)	13 A

Mechanical Attachment

Terminal Position Assurance	Yes
Strain Relief	Add By Accessory
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA GF
Centerline (Pitch)	4.44 mm[.175 in]

Dimensions

Connector Height	40.56 mm[1.597 in]
Product Width	20.83 mm[.82 in]
Product Length	43.21 mm[1.701 in]
Row-to-Row Spacing	9.12 mm[.359 in]
Compatible Insulation Diameter Range	1.35 – 3.05 mm[.053 – .12 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

--	--



Circuit Application	Power
---------------------	-------

Industry Standards

Degree of Protection	IP68, IP6K9K
Compatible With Agency/Standards Products	SAE J2030
UL Flammability Rating	12mm Flame Test per Standard UL-94

Packaging Features

Packaging Quantity	350
Packaging Method	Box

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-J41-DDRC DEUTSCH DT Receptacle Connectors	 TE Part # CAT-J67-DSCC16 DEUTSCH Size 16 Crimp Contacts	 TE Part # CAT-D487-P729 Dust Caps — DEUTSCH DT	 TE Part # CAT-D487-H342 DEUTSCH DT Headers
 TE Part # CAT-D487-W416 Wedgelocks: DEUTSCH DT	 TE Part # CAT-D48-ST273 DEUTSCH Solid Contacts	 TE Part # CAT-D48-SP729 DEUTSCH Sealing Plugs	 TE Part # DT-RT1 EXT TOOL, FRONT RELEASE
 TE Part # CAT-D487-CH8172 DEUTSCH DT Series Housings & Connectors	 TE Part # 1010-058-1206 SEAL, INTF, 12P, RED-ORG, SL RET, DT	 TE Part # 1062-14-0177 SOC, SF, SIZE 16, 14-18, SN/SN	

Also in the Series | DEUTSCH DT

 Automotive Connector Caps & Covers (19)	 Automotive Connector Locks & Position Assurance(87)	 Automotive Housings(706)	 Connector Backshells(61)
--	--	---	---



Connector Seals & Cavity Plugs(6)

Connector Strain Relief(28)

Insertion & Extraction Tools(3)

Other Automotive Connector Accessories(28)

PCB Headers & Receptacles(106)

Customers Also Bought

TE Part #WB-51SAR
WEDGE LOCK, 102P, PLG, GRY, RT, DRB, A

TE Part #747841-4
15 MSFL PLUG RA 318 (IN,FM,BL)

TE Part #DT04-12PA-CE04
DEUTSCH DT Receptacle Connectors

TE Part #DT06-12SD-CE04
DEUTSCH DT Plug Connectors

TE Part #1-770249-0
UMNL II SOK SN/AUNI/PHBZ LP

TE Part #9-103329-0
40 MODII HDR SRRA B/A .100 CL LF

TE Part #61366-1
AUTO MNL PIN PTPBR

Documents

Product Drawings
PLG, 12P, GRY, E, XCAP, A
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_DT06-12SA-CE04_B.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_DT06-12SA-CE04_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_DT06-12SA-CE04_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English