

DRB16-48SBE-L018

✓ ACTIVE

DEUTSCH | DEUTSCH DRB

TE Internal #: DRB16-48SBE-L018

Housing for Female Terminals, Wire-to-Wire, 48 Position, 3.81 mm / 4.7 mm / 6.71 mm [.15 in / .185 in / .264 in] Centerline, Sealable, Black

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH DRB Housings



Connector System: **Wire-to-Wire**
Number of Positions: **48**
Connector & Housing Type: **Housing for Female Terminals**
Centerline (Pitch): **3.81 mm, 4.7 mm, 6.71 mm [.15 in, .185 in, .264 in]**
Sealable: **Yes**

[All DEUTSCH DRB Housings \(19\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	Yes
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Blank Cavity Position	0
Connector Modification	Wire Router
Connector Seal Code	E Seal
Number of Positions	48
Number of Rows	6



Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	250 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Black
Connector & Keying Code	B

Contact Features

Contact Size	Size 12, Size 16, Size 20
Contact Type	Socket
Mating Pin Diameter	1.02 mm, 1.59 mm, 2.39 mm[.04 in][.063 in][.094 in]
Contact Current Rating (Max)	7.5 A, 13 A, 25 A

Mechanical Attachment

Terminal Position Assurance	Yes
Strain Relief	With
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA GF
Centerline (Pitch)	3.81 mm, 4.7 mm, 6.71 mm[.15 in][.185 in][.264 in]

Dimensions

Connector Height	66.19 mm[2.606 in]
Product Width	66.19 mm[2.606 in]
Product Length	35.71 mm[1.406 in]
Row-to-Row Spacing	.64 mm, 7.57 mm, 7.77 mm, 8.2 mm, 8.41 mm[.025 in][.298 in][.306 in][.323 in][.331 in]
Compatible Insulation Diameter Range	1.02 – 2.41 mm, 1.35 – 3.05 mm, 2.46 – 4.01 mm[.04 – .095 in][.053 – .12 in][.097 – .158 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
-----------------------------	----------------



Operating Temperature Range

-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Degree of Protection	IP68, IP6K9K
Compatible With Agency/Standards Products	SAE J2030

Packaging Features

Packaging Quantity	36
Packaging Method	Box

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # CAT-D48-SP729 DEUTSCH Sealing Plugs	 TE Part # DRB12-48PBE-L018 REC, 48P, BLK, E, CAP, B	 TE Part # CAT-J67-DSCC16 DEUTSCH Size 16 Crimp Contacts	 TE Part # CAT-D48-ST273 DEUTSCH Solid Contacts
 TE Part # DRBF-3AB FLANGE, MOUNT, 60/48P, BLK, DUAL, AB	 TE Part # DT-RT1 EXT TOOL, FRONT RELEASE	 TE Part # 3315-015-0005 PROTECT CVR, 48/60P, PLG, YEL, DRB	 TE Part # 1062-12-0144 SOC, SF, SIZE 12, 12-14, AU/SN
 TE Part # 1062-20-0622 SOC, SF, SIZE 20, 14-16, NI/NI	 TE Part # 1062-12-0222 SOC, SF, SIZE 12, 10, NI/NI	 TE Part # 1062-20-0244 SOC, SF, SIZE 20, 16-22, AU/SN	 TE Part # 1062-20-0322 SOC, SF, SIZE 20, 16-22, SLEVLESS, NI /NI
 TE Part # 1062-20-0377 SOC, SF, SIZE 20, 16-22, SLEVLESS, SN /SN	 TE Part # 1062-20-0277 SOC, SF, SIZE 20, 16-22, SN/SN	 TE Part # WB-48SB WEDGE LOCK, 48P, PLG, BLK, DRB, B	 TE Part # 1062-12-0166 SOC, SF, SIZE 12, 12-14, NI/SN
 TE Part # 1062-20-0222 SOC, SF, SIZE 20, 16-22, NI/NI	 TE Part # 1062-20-0122 SOC, SF, SIZE 20, 16-22, NI/NI	 TE Part # 1062-20-0144 SOC, SF, SIZE 20, 16-22, AU/SN	 TE Part # 1062-12-0244 SOC, SF, SIZE 12, 10, AU/SN

Also in the Series | **DEUTSCH DRB**



Automotive Connector Caps & Covers (1)



Automotive Connector Locks & Position Assurance(20)



Automotive Housings(19)



Connector Strain Relief(1)



Insertion & Extraction Tools(1)



Other Automotive Connector Accessories(6)

Customers Also Bought



TE Part #DRB12-48PBE-L018
DEUTSCH DRB Housings



TE Part #WB-48PB
DEUTSCH DRB Wedgelocks



TE Part #DRBF-2B
FLANGE, MOUNT, 60/48P, BLK, B



TE Part #HD34-18-21PN-059
REC,21P,AL,N, CBL CLMP BT, DRAIN, 20,P,MC



TE Part #2293821-1
DEUTSCH HDP20 Housings



TE Part #DRB48-60-BT
BOOT, 48/60P, PLG/REC, ST, BLK

Documents

Product Drawings
PLG, 48P, BLK, E, CAP, B
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_DRB16-48SBE-L018_99_c-drb16-48sbe-l018-99.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_DRB16-48SBE-L018_99_c-drb16-48sbe-l018-99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_DRB16-48SBE-L018_99_c-drb16-48sbe-l018-99.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English