

Neohm | Neohm ROX

TE Internal #: 6-1676123-6

General Purpose Resistor, Metal Oxide Film, .5 W, 430 ohm, 5 %,
±350 ppm/°C, Axial-Leaded, Copper Termination, 7.2 x 2.5 mm,
Ammo Packed, Neohm ROX

[View on TE.com >](#)[Passive Components > Resistors > Through-Hole Resistors](#)Resistor Type: **General Purpose Resistor**Element Type: **Metal Oxide Film**Power Rating: **.5 W**Resistance Class: **Up to 1kΩ**Resistance Value: **430 Ω**

Features

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Metal Oxide Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	250 V
Power Rating	.5 W
Resistance Class	Up to 1kΩ
Resistance Value	430 Ω
Passive Component Tolerance	5 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material

Copper

Number of Terminations

2

Dimensions

Passive Component Dimensions

7.2 x 2.5 mm

Usage Conditions

Operating Temperature Range

-55 – 155 $^{\circ}$ C

Temperature Coefficient

 ± 350 ppm/ $^{\circ}$ C**Packaging Features**

Packaging Method

Ammo Packed

Product ComplianceFor compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024 (241)

Candidate List Declared Against: JUNE 2023 (235)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Wave solder capable to 265 $^{\circ}$ C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Neohm ROX



Customers Also Bought





TE Part #4-2176611-6
EP 2W (SS) 75R 5%

Documents

Product Drawings

[1/2W SM M/OX 5% 430R](#)

English

Datasheets & Catalog Pages

[Flame Proof Power Metal Oxide Film Resistors - Type ROX Series - Tyco Electronics Passives](#)

English