




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings > AMP COMMON TERMINATION HOUSINGS



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **8**
Centerline (Pitch): **2 mm [.079 in]**

[All AMP COMMON TERMINATION HOUSINGS \(176\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	8
Number of Rows	1

Body Features

Primary Product Color	Gray
-----------------------	------

Contact Features

Contact Current Rating (Max)	3 A
------------------------------	-----

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

--	--



Mating Retention Type	Lock
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	2 mm[.079 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-3984552-BHTHVS
CT Box Header SMT: Vert, Shrouded



TE Part # 292133-8
CT P/HDR ASSY BOX V 8P W/O KIN



TE Part # CAT-3983178-PHBXVD
CT 2mm Post Header Asmbly: Box V DIP



TE Part # CAT-3980407-RHRRRA
CT 2mm Header Assembly: Right Angle



TE Part # 292206-8
MINI CT SGL DIP H 8P NAT



TE Part # CAT-AM7017-H342
AMP COMMON TERMINATION HEADERS



TE Part # CAT-3984552-PHITPS
CT Post Header Assembly: Part. Shrouded



TE Part # 58074-1
MTA 50/100/156 MANUAL TOOL FRAME



TE Part # 58372-1
HEAD (IDC) 2MM C.T. W/O TL



TE Part # 292228-8
1.5 MINI CT SGL H SMT W/O BOSS



TE Part # 292227-8
1.5 MINI CT SGL H SMT W BOSS 8



TE Part # 292254-8
CT RELAY HDR ASSY 8P NAT



TE Part # 292215-8
MINI CT SGL RELAY 8P NAT



TE Part # 292207-8
MINI CT SGL DIP V 8P NAT



TE Part # 292182-8
PLUG ASS'Y OF HYB DRAWER 12P



TE Part # 292164-8
CT P/HDR BOX H ASSY 8P T/P NAT




TE Part # CAT-3980408-PHDWKV
CT 2mm Post Header Assembly with Kink - Vertical



TE Part # 1-292254-7
CT RELAY HDR ASSY 8P NAT



TE Part # 292185-8
REC ASS'Y OF HYB DRAWER 12P



TE Part # 292165-8
CT P/HDR BOX V 8P T/P NAT

Also in the Series | AMP CT






Connector Contacts(8)



Connector Hardware(46)



PCB Headers & Receptacles(756)



Wire-to-Board Connector Assemblies & Housings(255)


Customers Also Bought



TE Part #1-292254-0
CT RELAY HDR ASSY 10P NAT



TE Part #353293-7
MINI CT MT REC ASSY 7P GRAY



TE Part #179970-1
250 HSG. PL EX REC.




TE Part #179974-1
250 PL EX REC. 18-14AWG PTBR




TE Part #4-292246-2
1.5 MINI CT LATTICE REC KEY B




TE Part #4-353293-0
1.5MM CT MT REC ASSY 20P BLACK



TE Part #9-292112-4
MT REC ASSY (#26,28)



TE Part #9-292112-1
MT REC ASSY (#26,28)



TE Part #080-0014
CABLE,U.FL to SMA Bulkhd 1.13mm
Dia,210m



TE Part #9-292112-2
MT REC ASSY (#26,28)

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_2-179694-8_F.2d_dxf.zip
- English
- Customer View Model
- ENG_CVM_CVM_2-179694-8_F.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_2-179694-8_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED](#)

English

Product Specifications

Application Specification

English

[Crimping of AMP 2.0mm Pitch, CT Crimp Typell Rec Contact](#)

English

Application Specification

English