

5-5175474-5  ACTIVE

## CHAMP


TE Internal #: 5-5175474-5

Receptacle, 40 Position, Printed Circuit Board, Power & Signal,  
Docking Connectors

[View on TE.com >](#)



Connectors > Docking Connectors



Docking Connector Style: **Receptacle**

Number of Positions: **40**

Connector & Contact Terminates To: **Printed Circuit Board**

Circuit Application: **Power & Signal**

## Features

### Product Type Features

Docking Connector Style	Receptacle
-------------------------	------------

Connector & Contact Terminates To	Printed Circuit Board
-----------------------------------	-----------------------

### Configuration Features

Number of Positions	40
---------------------	----

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)
--	---

Candidate List Declared Against: JUNE 2024 (241)
--

Does not contain REACH SVHC
-----------------------------


Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Wave solder capable to 260°C
---------------------------	------------------------------

[Product Compliance Disclaimer](#)

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 5-5175473-5  
.050CL,CHAMP,VERT PLUG,40 POSN

## Customers Also Bought




TE Part #3-644456-6  
06P MTA100 HDR ASSY (NARROW)



TE Part #2141404-1  
20POS, NANOMQS, REC HSG, CODE A



TE Part #T4140012121-000  
M12, REAR MOUNT, MALE, A, 12P,  
SOLDER PCB



TE Part #747932-1  
09 SHIELD ENCLOSURE HDP



TE Part #1734099-4  
Champ 050 series, plug assembly



TE Part #282403-1  
MINI MIC SRS REC CONT



TE Part #2-1703930-1  
NANOMQS, RECEPTACLE TERMINAL



TE Part #D42391-000  
RNF-100-MINI-SPL-3/32-BK



TE Part #BB8965CN  
WHIP,MC,CC,896-970MHz 933,5,BK,  
NGP,

## Documents

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5-5175474-5\\_O.2d\\_dxf.zip](#)

English

### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5-5175474-5\\_O.3d\\_jgs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_5-5175474-5\\_O.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

#### Product Specification

English