



Application Tooling > Hand Crimping Tools



Ratchet Configuration: **Operator Releasable & Adjustable**

TE Certification: **Cannot be Certified**

Power Technology Type: **Manual**

Tooling Type: **Handle Assembly**

Features

Other

Ratchet Configuration	Operator Releasable & Adjustable
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	Handle Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # 3-640428-8
08P MTA156 CONN ASSY 22AWG RED



TE Part # 5-103956-8
2X9 MTE RCPT SR LATCH .100CL




TE Part # 3-640429-7
07P MTA156 CONN ASSY 24AWG WHT



TE Part # 4-640426-0
10P MTA156 CONN ASSY 18AWG ORA

Customers Also Bought




TE Part #643075-8
08P MTA100 MOLDED COVER



TE Part #58372-1
HEAD (IDC) 2MM C.T. W/O TL



TE Part #58443-1
MTA 156 CRIMP HEAD PRODUCTION FEED THRU



TE Part #643067-6
06P MTA156 MOLDED COVER



TE Part #4-643817-2
12P MTA156 CONN ASSY 18AWG LF



TE Part #4-643819-6
16P MTA156 CONN ASSY 22AWG LF



TE Part #58336-1
HEAD (IDC) MODU MTE W/O TL



TE Part #58063-2
HEAD (IDC) HDE-20 W/O TL



TE Part #58246-2
MTA 100 CRIMP HEAD PRODUCTION DISCRETE



TE Part #640632-3
MTA .156 CONTACT BRNBNR

Documents

Datasheets & Catalog Pages
MTA Portable Tooling Solutions

English

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

Bottoming Dies

English

AMPMODU MTE INTERCONNECT SYSTEM



English

Instruction Sheets

Instruction Sheet (U.S.)

English