

HDP24-24-21SE-L017

✓ ACTIVE

DEUTSCH | DEUTSCH HD, DEUTSCH HDP

TE Internal #: HDP24-24-21SE-L017

Housing for Female Terminals, Wire-to-Panel, 21 Position, Sealable, Black, Wire & Cable, Power, Panel Mount, -55 – 125 °C [-67 – 257 ° F], Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH HDP20 Housings



Connector System: **Wire-to-Panel**

Number of Positions: **21**

Connector & Housing Type: **Housing for Female Terminals**

Sealable: **Yes**

Mating Pin Diameter: **1.6 mm, 2.4 mm [.063 in, .094 in]**

[All DEUTSCH HDP20 Housings \(357\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	Yes
Connector Shape	Circular
Connector System	Wire-to-Panel
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Contact Retainer

Configuration Features

Blank Cavity Position	0
Connector Modification	Ring Adapter
Connector Seal Code	E Seal
Number of Positions	21

Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	250 V

Body Features



Cable Exit Angle	180°
Primary Product Color	Black

Contact Features

Contact Size	Size 12, Size 16
Contact Type	Socket
Mating Pin Diameter	1.6 mm, 2.4 mm[.063 in][.094 in]
Contact Current Rating (Max)	13 A, 25 A

Mechanical Attachment

Terminal Position Assurance	No
Strain Relief	Without
Mating Alignment Type	Polarization Slot
Mating Alignment	With
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	PA 66 GF
------------------	----------

Dimensions

Connector Height	45.8 mm[1.8 in]
Product Width	47.6 mm[1.87 in]
Product Length	50.8 mm[2 in]
Compatible Insulation Diameter Range	1.4 – 3.8 mm, 3.6 – 5.2 mm[.055 – .15 in][.14 – .204 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Degree of Protection	IP67
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	30
Packaging Method	Tray



Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D48-SP729
DEUTSCH Sealing Plugs



TE Part # HDP26-24-21PE-L017
PLG, 21P, BLK, E, RNG, 12/16, P




TE Part # CAT-H396-RC8382
Receptacle Protective Caps —
DEUTSCH HDP20









TE Part # CAT-H396-B128
DEUTSCH HDP20 Backshells



 TE Part # HD30-24BT-BK BOOT, 24SZ, ST, BLK	 TE Part # 24-D-PUNCH D-HOLE PUNCH, SIZE 24	 TE Part # 0411-337-1205 EXT TOOL, SIZE 12, 12-14 AWG, E, ORG	 TE Part # 16-04477 GASKET, 24SZ, BLK, HD30 ORG
 TE Part # HD30-24BT BOOT, 24SZ, ST, GRY	 TE Part # HD30-24BT-90-BK BOOT, 24SZ, RA, BLK	 TE Part # 0411-336-1605 EXT TOOL, SIZE 16, 16-20 AWG, E, DRK BLU	 TE Part # 62036-40 62036 HDP24 FLANGE-SEAL silicone 60shore

Also in the Series

DEUTSCH HD

 Automotive Connector Caps & Covers (32)	 Automotive Housings(768)	 Connector Backshells(29)	 Connector Seals & Cavity Plugs(10)
 Connector Strain Relief(5)	 Insertion & Extraction Tools(11)	 Other Automotive Connector Accessories(11)	 PCB Headers & Receptacles(1)

Also in the Series

DEUTSCH HDP



Automotive Connector Caps & Covers
(4)



Automotive Housings(357)



Connector Backshells(8)



Connector Seals & Cavity Plugs(1)



Insertion & Extraction Tools(11)



Other Automotive Connector
Accessories(5)

Customers Also Bought



TE Part #HDP26-24-9PE-L017
DEUTSCH HDP20 Housings




TE Part #2428-008-2405
DEUTSCH HDP20 Backshells



TE Part #1060-16-0722
PIN, SF, SIZE 16, 14-18, NI/SN



TE Part #1478768-3
ANTI-VIB NYLON GLD 20MM GREY



TE Part #EP-24
CAP ID=35.31 H=16

Documents

Product Drawings

REC, 21P, BLK, E, RNG, 12/16, S

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_HDP24-24-21SE-L017_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_HDP24-24-21SE-L017_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_HDP24-24-21SE-L017_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English