


Passive Components &gt; Resistors &gt; Through-Hole Resistors &gt; Wirewound Resistor: Vertical Mount

Resistor Type: **Power Resistor**Element Type: **Wire Wound**Power Rating: **10 W**Resistance Class: **Up to 1k $\Omega$** Resistance Value: **.68  $\Omega$** [All Wirewound Resistor: Vertical Mount \(202\)](#)

## Features

### Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

### Configuration Features

Number of Resistors	1
---------------------	---

### Electrical Characteristics

Power Rating	10 W
Resistance Class	Up to 1k $\Omega$
Resistance Value	.68 $\Omega$
Passive Component Tolerance	5 %

### Body Features

Lead Type	Radial-Leaded
-----------	---------------

### Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

### Dimensions

Passive Component Dimensions	51 x 13 x 9 mm
------------------------------	----------------

### Usage Conditions

Operating Temperature Range	-55 – 250 °C
Temperature Coefficient	$\pm 300$ ppm/°C

### Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

### Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

#### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # CAT-C339-SQ1  
Wirewound Resistor: Vertical Mount

## Also in the Series | CGS SQ



Through-Hole Resistors(662)

## Customers Also Bought




TE Part #1-1623788-5  
Wirewound Resistor: Vertical Mount




TE Part #2-1419104-1  
T9AS1D22-24



TE Part #678853-000  
CWT-7



TE Part #160314-5  
250 PIDG FASTON REC



TE Part #9-160313-5  
250 PIDG FASTON REC



TE Part #62307-2  
AMVAR SPLC 1500-5000 016TPBR



TE Part #1676380-2  
RN 0805 57K6 0.1% 10PPM 1KRL

## Documents

### Product Drawings

#### SQM10 R68 5% (WIRE)

English

### Datasheets & Catalog Pages

#### 4-1773460-6\_RESISTIVE\_SOLUTIONS\_RAIL

English

[1309350\\_PASSIVE\\_COMPONENT](#)

English

[High Power Resistors - Type SQ Series](#)

English

[8-1773459-4\\_POWER\\_FILTERING\\_AND\\_RESISTIVE\\_SOLUTIONS\\_FOR\\_ELEVATORS\\_AND\\_ESCALATORS](#)

English