



Terminals & Splices > Automotive Terminals > TIMER, RECEPTACLE AND TAB



Terminal Type: **Receptacle**
Mating Tab Width: **2.8 mm [.11 in]**
Mating Tab Thickness: **.8 mm [.031 in]**
Terminal Transmits: **25 – 40 A (Power)**
Wire Size: **20 – 17 AWG**

[All TIMER, RECEPTACLE AND TAB \(324\)](#)

Features

Product Type Features

Sealable	No
Primary Locking Feature	Locking Lance

Contact Features

Contact Size	2.8mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	30 A
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.8 mm[.031 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Compatible Insulation Diameter Range	1.4 – 2.3 mm
--------------------------------------	--------------



Wire Size	.5 – 1 mm²
Wire Size Search	17 AWG, 18 AWG, 19 AWG, 20 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C[176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Compatible With Agency/Standards Products	DIN 72 551 Part 6, DIN ISO 6722 part 3
---	--

Packaging Features

Packaging Quantity	4000
Packaging Method	Carton

Other

Terminal Transmits	25 – 40 A (Power)
--------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 4-1579007-3 EXTRACTION TOOL KIT	 TE Part # 1-1579007-6 EXTRACTION TOOL	 TE Part # CAT-T4827-CH8172 Timer Connector Housing	 KIT TE Part # 7-2151092-7 OCEAN_2.0_SPARE_PART_KIT-080F110OV
 TE Part # 2151092-1 OCEAN_2.0_APPLICATOR-S-080F110OV-RSM	 TE Part # 2151092-2 OCEAN_2.0_APPLICATOR-S-080F110OV-RSA	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 5-2151092-1 OCEAN_2.0_APPLICATOR-S-080F110OV-RSM
 TE Part # 5-2151092-2 OCEAN_2.0_APPLICATOR-S-080F110OV-RSA	 KIT TE Part # 7-2266186-7 OC-080F110OV-752-CRIMPTOOLINGKIT	 KIT TE Part # 7-2266286-7 OC-079SP110SP-LP-CRIMPTOOLINGKIT	

Also in the Series | Junior Power Timer



Automotive Connector Caps & Covers (9)



Automotive Connector Locks & Position Assurance(8)



Automotive Housings(323)



Automotive Terminals(189)



Busbars & Terminals(1)



Connector Seals & Cavity Plugs(9)



Insertion & Extraction Tools(8)



Module Components(1)



Other Automotive Connector Accessories(2)



Special Purpose Terminals(2)

Customers Also Bought



TE Part #M902-2193
BKSHL, 9SZ, CBL SZ .430-.570, HD10



TE Part #3-1534903-5
60POS MIXED MQS REC SEALED
COD 2-3-6-7



TE Part #42113-2
SPADE TERMINAL 12-10 AWG TPBR



TE Part #2132781-9
09P EP-II HOUSING, NATURAL




TE Part #1971789-1
CPA



TE Part #520197P061
RT-3-NO.2-0-1.5IN



TE Part #3-1971773-4
PTL 1X4 PLUG HSG STD TEMP KEY C
BLU



TE Part #2305570-1
Strip Terminal Cutter-Side Feed-No
Crimp



Documents

CAD Files

Customer View Model

[ENG_CVM_965901-1_A2.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_965901-1_A2.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_965901-1_A2.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English