




Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spring Spade Terminal**  
Wire Size: **509 – 3260 CMA**  
Stud Size: **#10**

Features

Product Type Features

|                                        |                    |
|----------------------------------------|--------------------|
| Stud Size                              | #10                |
| Sealable                               | No                 |
| Wire Insulation Support Retention Type | Insulation Support |

Electrical Characteristics

|                |               |
|----------------|---------------|
| Voltage Rating | 1000 V, 600 V |
|----------------|---------------|

Body Features

|                         |        |
|-------------------------|--------|
| Insulation Sleeve Color | Red    |
| Stripe Color            | Red    |
| Product Weight          | .155 g |

Contact Features

|                           |                       |
|---------------------------|-----------------------|
| Spade Terminal Type       | Spring Spade Terminal |
| Barrel Type               | Closed                |
| Terminal Orientation      | Straight              |
| Terminal Plating Material | Tin                   |

Mechanical Attachment



|                         |      |
|-------------------------|------|
| Wire Insulation Support | With |
|-------------------------|------|

Dimensions

|                                      |                               |
|--------------------------------------|-------------------------------|
| Wire Size                            | 509 – 3260 CMA                |
| Stud Diameter                        | 4.83 mm[.19 in]               |
| Tongue Thickness                     | .79 mm[.031 in]               |
| Product Length                       | 23.37 mm[.92 in]              |
| Compatible Insulation Diameter (Max) | 3.56 mm[.14 in]               |
| Compatible Insulation Diameter Range | 2.67 – 3.56 mm[.105 – .14 in] |

Usage Conditions

|                             |                     |
|-----------------------------|---------------------|
| Insulation Option           | Partially Insulated |
| Operating Temperature Range | 105 °C[221 °F]      |

Operation/Application

|                                       |        |
|---------------------------------------|--------|
| Compatible With Wire Base Material    | Copper |
| Compatible With Wire Plating Material | Tin    |

Industry Standards

|                               |    |
|-------------------------------|----|
| Government Qualified Terminal | No |
|-------------------------------|----|

Packaging Features

|                    |             |
|--------------------|-------------|
| Packaging Quantity | 1000        |
| Packaging Method   | Loose Piece |

Product Compliance

For compliance documentation, visit the product page on TE.com>



|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                  |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                                                                                                        |                                                                                                                                           |                                                                                                                                            |                                                                                                                                                          |
|--------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 47386-4<br/>DAHT PG PIDG 26-16 ASSY</p>                |  <p>TE Part # 58433-3<br/>PRO CR ASSY, RBY IS9252</p>  |  <p>TE Part # 59250<br/>T-HEAD PIDG 26-14 ASSY</p>     |  <p>TE Part # 58423-1<br/>DIE, RBY IS9252</p>                        |
|  <p>TE Part # 59824-1<br/>TETRA-CRIMP PIDG PG FASTON 22-10 ASSY</p> |  <p>TE Part # 47386<br/>DAHT PG PIDG 26-16 ASSY</p>   |  <p>TE Part # 539691-2<br/>ERGO DIE R.B.Y</p>         |  <p>TE Part # 2063030-1<br/>SDE DIESET, RBY, UL</p>                 |
|  <p>TE Part # 47806-2<br/>DIES PIDG 22-16 DIE SET</p>               |  <p>TE Part # 59300<br/>T-HEAD PIDG PG 26-16 ASSY</p> |  <p>TE Part # 169400<br/>CERTI-LOK FRAME W/O DIES</p> |  <p>TE Part # 2392021-2<br/>RED BATTERY DAHT KIT 220V (47689-4)</p> |
|  <p>TE Part # 2392021-1<br/>RED BATTERY DAHT KIT 110V (47689-4)</p> |  <p>TE Part # 169404<br/>CERTI-LOK DIE</p>            |  <p>TE Part # 1SET191001R0000<br/>CRIMP-HT</p>        |  <p>TE Part # 1SET191002R0000<br/>TET CRIMP-HT</p>                  |





Also in the Series | **PLASTI-GRIP**




Compression Connectors(3)



Crimp Wire Pins, Tabs & Ferrules(19)



Ring Terminals(300)




Spade Terminals(160)



Splices(46)

Customers Also Bought



TE Part #566586-000  
202K163-25/225-0



TE Part #5-1478762-1  
Metal backshell 9 way Top Entry-KIT



TE Part #5-103080-5  
07 MODII HDR SRST SHRD .100CL




TE Part #2071566-4  
PT78A2P



TE Part #6-2176381-3  
RQ 0805 54K9 0.1% 10PPM 5K RL



TE Part #1534807-1  
HD20 COVER KIT 15P



TE Part #106462-1  
2P.FASTIN-ON HSG.



TE Part #6-103361-2  
14 MODII HDR SRRA SHRD LF



TE Part #2299940-6  
ZQSFP+ STACKED REC ASSEMBLY  
2X1,HS



TE Part #1-1904045-2  
V23333Z1001A008-EV-100





Documents

Product Drawings

PG SPR SPD 22-16COM22-18MIL 10

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_53242-1\_J.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_53242-1\_J.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_53242-1\_J.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_53242-1\_K.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_53242-1\_K.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_53242-1\_K.2d\_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English

UL Report

English