

EDT2 ENHANCED DIN RAIL SURGE PROTECTION CLASS II, 4+0 MODE, 277 V UN

CATALOG NUMBER

EDT235040R



CERTIFICATIONS



FEATURES

Includes nVent ERICO TD Technology to ensure reliability throughout adverse voltage conditions

Enhanced temporary over voltage (TOV) withstand capability

External back-up fuse is not required up to 315 A (IEC only)

Compact, yet high surge rated pluggable design, using minimum DIN rail width

Retaining clip ensures enhanced vibration and shock resistance performance

Red/Green status indication and change-over contacts standard for remote monitoring

PRODUCT ATTRIBUTES

Nominal System Voltage (Un): 277 V

Max Continuous Operating Voltage (Uc): 350 V

Nominal Discharge Current (In), IEC: 20kA 8/20 μ s

Max Discharge Current (Imax), IEC: 50kA 8/20 μ s

Voltage Protection Level (Up): 1750V

Back-Up Fuse @ Isccr: 250 A @ 50 kA; 315 A @ 25 kA


Frequency: 50 - 60 Hz

Response Time: 25 ns Max

Protection Modes: L-PE;N-PE

| |
|---|
| Short Circuit Current Rating (Isc): 25kA;50kA |
| Temporary Over Voltage 120 min (Ut/mode): 529 V Withstand |
| Nominal Discharge Current (In), UL: 20kA 8/20 μ s |
| Short Circuit Current Rating (SCCR): 200kA |
| Voltage Protection Rating (VPR): 1200V |
| Technology: Thermal Disconnect |
| Connection, Solid: #2 max |
| Connection, Stranded: #4 max |
| Torque (TQ): 3.32 ft·lbf |
| Humidity: 5 - 95 |
| Temperature: -31 to 185 °F |
| Enclosure Material: UL® 94V-0 Thermoplastic |
| Enclosure Rating: IP 20 |
| Mounting: 35 mm top hat DIN rail |
| Remote Contact Switching Capacity: 1 A @ 250 VAC;1 A @ 125 VAC;0.5 A @ 48 VDC;0.5 A @ 24 VDC;0.5 A @ 12 VDC |
| Remote Contacts: Yes |
| Status Indication: Mechanical flag |
| Depth (D): 2.72" |
| Height (H): 3.54" |
| Width (W): 2.84" |
| Unit Weight: 1.22 lb |
| Certification Details: UL® 1449 Edition 5 Type 1CA |
| Complies With: EN 61643-11 Type 2;IEC® 61643-11 Class II |
| Replacement Module: EDT2350M |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



nVent.com

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF

TRACER