




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: **Closed Ring Tongue Terminal**

Wire Size: **2582 – 6529 CMA**

Stud Size: **#8, M4**

Features

Product Type Features

Shape Description	Anti-Rotational/Grounding
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Contact Base Material	Brass
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Unplated
Contact Underplating Material	None

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.13 in
--	--------



Wire Size	2582 – 6529 CMA
Stud Diameter	3.68 mm[.145 in]
Tongue Thickness	.76 mm[.03 in]
Product Length	19.56 mm[.77 in]
Barrel Inside Diameter	2.03 mm, 3.93 mm[.08 in][.155 in]
Compatible Insulation Diameter (Max)	4.32 mm[.17 in]
Compatible Insulation Diameter Range	3.3 – 4.32 mm[.13 – .17 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	9000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2150653-1
OCEAN_2.0_APPLICATOR-E-140F220O-REM

TE Part # 2150653-2
OCEAN_2.0_APPLICATOR-E-140F220OA-REA

TE Part # 7-2150653-7
OCEAN_2.0_SPARE_PART_KIT-140F220O

Customers Also Bought

TE Part #350509-1
RING 22-16 AWG BR

TE Part #62428-2
250 FASTON REC 12-10 AWG TPBR

TE Part #63130-2
SPLICE REC. 1500-5000 .020 BR

TE Part #61436-1
RING 22-16 AWG BR

TE Part #640271-3
RING 22-18 AWG TPST

TE Part #130446
PIDG RING

TE Part #62139-1
187 FASTON REC 20-16 AWG TPBR

TE Part #60573-2
187 FASTON REC 24-20 BR

TE Part #1601755-1
L165D20B=RTM 4000-13000



Documents

Product Drawings
RING CRIMP 16-12 AWG BR
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_61624-1_R_c-61624-1-r.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_61624-1_R_c-61624-1-r.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_61624-1_R_c-61624-1-r.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Application Specification
English