



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.32 – .82 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Connection Capacity	Single
Compatible With Wire & Cable Type	Discrete Wire

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Terminal Material Thickness	.4 mm[.015 in]
Product Length	19.6 mm[.77 in]
Compatible Insulation Diameter Range	1.52 – 2.54 mm[.06 – .1 in]
Wire Size	.32 – .82 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	2500
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 91514-1 CCII FASTON 250 REC 22-18 ASSY	TE Part # 2151242-1 OCEAN-2.0-APPLICATOR-S-090F120O-RSM	TE Part # 2151242-2 OCEAN-2.0-APPLICATOR-S-090F120OA-RSA	TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp
TE Part # 5-2151242-1 OCEAN-2.0-APPLICATOR-S-090F120O-RSM	TE Part # 5-2151242-2 OCEAN-2.0-APPLICATOR-S-090F120O-RSA	TE Part # 7-2151242-7 OCEAN_2.0_SPARE_PART_KIT-090F120O	

Also in the Series | FASTON 250

Compression Connectors(4)	Crimp Terminal Housings(132)	Insertion & Extraction Tools(6)	Magnet Wire Terminals(1)



PCB Terminals(134)



Quick Disconnects(426)



Splices(4)

Customers Also Bought



TE Part #5748476-1
KIT,PLUG,62P,HDP-22,SHLD ENCLS



TE Part #2-32947-1
PG R 22-16 COMM 22-18 MIL 6



TE Part #2-32949-1
PG R 22-16 COMM 22-18 MIL 10



TE Part #41531-1
250 FASTON FLAG REC 18-12 AWG NPST



TE Part #61944-1
250 FASTON REC 18-14 AWG BR



TE Part #60772-3
RING CRIMP 18-14 AWG TPBR



TE Part #63315-1
250 FASTON FLAG 18-14 AWG BR



TE Part #42801-1
187 FASTON REC 20-16 AWG BR



TE Part #61436-1
RING 22-16 AWG BR



TE Part #53440-1
ELECTRO-TAP, 18-14 AWG RUN&TAP

Documents

Product Drawings

250 FASTON REC 22-18 AWG BR

English

CAD Files

Customer View Model

ENG_CVM_CVM_61988-1_AK.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_61988-1_AK.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_61988-1_AK.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[82004 FASTON Terminals \(Insulated and Uninsulated\) Catalog - FASTON Receptacles Section](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English