



Terminals & Splices > Automotive Terminals > ROUND CONNECTOR SYSTEM, PIN AND SOCKET



Terminal Type: **Socket**

Mating Pin Diameter: **2.5 mm [.098 in]**

Terminal Transmits: **25 – 40 A (Power)**

Wire Size: **.5 – 1 mm²**

All ROUND CONNECTOR SYSTEM, PIN AND SOCKET (48)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Locking Lance

Contact Features

Contact Size	2.5mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	40 A
Crimp Type	F-Crimp
Terminal Type	Socket
Mating Pin Diameter	2.5 mm[.098 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Product Terminates To

Wire

Dimensions

Compatible Insulation Diameter Range	1.4 – 2.1 mm[.055 – .083 in]
Wire Size	.5 – 1 mm²
Wire Size Search	17 AWG, 18 AWG, 19 AWG, 20 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C[176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Quantity	3200
Packaging Method	Reel

Other

Terminal Transmits	25 – 40 A (Power)
--------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1579007-8 EXTRACTION TOOL	 TE Part # 2-1579024-5 HAND TOOL 2,5 MM DIA. CONTACTS 0,5-1,0	 TE Part # 1703021-1 DIA 2.5MM CONTACT WITH WELDING FLAG	 TE Part # 2266254-1 OCEAN-2.0-APPLICATOR-S- 080F1000-RSM
 TE Part # 2266254-2 OCEAN-2.0-APPLICATOR-S- 080F1000-RSA	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 2837603-1 APPLICATOR TO MAKE LOOSE PC TERMINAL-RSM	 TE Part # 7-2266254-7 OCEAN_2.0_SPARE_PART_KIT- 080F1000
 TE Part # 7-2837603-7 TOOLING KIT TO MAKE LOOSE PIECE TERMINAL	 TE Part # 964197-1 AM RINGZUNGE MIF	 TE Part # 2837603-2 APPLICATOR TO MAKE LOOSE PC TERMINAL-RSA	

Also in the Series | Round Connector System



Automotive Connector Caps & Covers (3)



Automotive Housings(10)



Automotive Terminals(48)



Connector Seals & Cavity Plugs(5)



Insertion & Extraction Tools(8)


Customers Also Bought



TE Part #2-323916-3
TERMINAL,PIDG R IR 24 8



TE Part #1-967325-2
2,5MM BU-GEH 3P



TE Part #1487595-1
USB, A-B, 28/26, BLACK, 1.0M



TE Part #770018-1
03P UMNLI IN-LNE PLUG HSG KIT




TE Part #964202-1
STD TIMER CONTACT




TE Part #2176345-2
CRGCQ 1210 12R 1%




TE Part #DT06-12SA-B016
PLG, 12P, GRY, N, ENH KEY, A



TE Part #929963-1
STIFTKONTAKT 2,5MMD



TE Part #828986-1
DICHT-STOPFEN



TE Part #927389-1
PL 3P HOUSING PA66 BLACK

Documents



Product Drawings

SOCKET CONTACT 2,5MMD

German

CAD Files

Customer View Model

ENG_CVM_929970-1_A5.3d_igs.zip

English

Customer View Model

ENG_CVM_929970-1_A5.3d_stp.zip

English

Customer View Model

ENG_CVM_929970-1_A5.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

Product Specifications

Application Specification

English

Application Specification

German

Application Specification

English