




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**  
PCB Mount Orientation: **Vertical**  
Connector System: **Board-to-Board**  
Number of Positions: **3**  
Number of Rows: **1**

Features

Product Type Features

|                                   |                       |
|-----------------------------------|-----------------------|
| PCB Connector Assembly Type       | PCB Mount Header      |
| Connector System                  | Board-to-Board        |
| Header Type                       | Breakaway             |
| Sealable                          | No                    |
| Connector & Contact Terminates To | Printed Circuit Board |

Configuration Features

|                                  |              |
|----------------------------------|--------------|
| Connector Contact Load Condition | Fully Loaded |
| PCB Mount Orientation            | Vertical     |
| Number of Positions              | 3            |
| Number of Rows                   | 1            |
| Board-to-Board Configuration     | Parallel     |

Electrical Characteristics

|                                       |          |
|---------------------------------------|----------|
| Insulation Resistance                 | 5000 MΩ  |
| Dielectric Withstanding Voltage (Max) | 750 Vrms |



Body Features

|                       |       |
|-----------------------|-------|
| Primary Product Color | Green |
|-----------------------|-------|

Contact Features

|                                                         |                                          |
|---------------------------------------------------------|------------------------------------------|
| Mating Square Post Dimension                            | .63 mm[.025 in]                          |
| PCB Contact Termination Area Plating Material Thickness | 3 μm                                     |
| Contact Shape & Form                                    | Square                                   |
| Contact Underplating Material                           | Nickel                                   |
| PCB Contact Termination Area Plating Material           | Tin                                      |
| Contact Base Material                                   | Phosphor Bronze                          |
| Contact Mating Area Plating Material                    | Gold or Gold Flash over Palladium Nickel |
| Contact Mating Area Plating Material Thickness          | .8 μm[31.5 μin]                          |
| Contact Type                                            | Pin                                      |
| Contact Current Rating (Max)                            | 5 A                                      |

Termination Features

|                                          |                       |
|------------------------------------------|-----------------------|
| Square Termination Post & Tail Dimension | .63 mm[.025 in]       |
| Termination Post & Tail Length           | 2.5 mm[.099 in]       |
| Termination Method to PCB                | Through Hole - Solder |

Mechanical Attachment

|                         |             |
|-------------------------|-------------|
| Mating Alignment        | Without     |
| PCB Mount Retention     | Without     |
| PCB Mount Alignment     | Without     |
| Connector Mounting Type | Board Mount |

Housing Features

|                    |                |
|--------------------|----------------|
| Centerline (Pitch) | 2.54 mm[.1 in] |
| Housing Material   | PBT            |

Dimensions

|                             |                 |
|-----------------------------|-----------------|
| PCB Thickness (Recommended) | 1.4 mm[.055 in] |
|-----------------------------|-----------------|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Housing Temperature Rating  | Standard                   |
| Operating Temperature Range | -65 – 105 °C[-85 – 221 °F] |

Operation/Application

|                     |        |
|---------------------|--------|
| Circuit Application | Signal |
|---------------------|--------|



Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Packaging Features

|                    |        |
|--------------------|--------|
| Packaging Quantity | 2000   |
| Packaging Method   | Carton |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                  |
| Solder Process Capability                     | Wave solder capable to 265°C                                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 215297-3  
3P HV100 REC CON. TE, 7.0MM



TE Part # 1241152-3  
3P HV100 REC. CON, SMD, GOLD, BLISTER



TE Part # 829265-3  
3P HV100 REC.CON. B/TE,6,2,NO KINK



TE Part # 216602-3  
HV190 REC ASSY 1X 3P



TE Part # 215299-3  
3P HV100 REC CON. TE, 8.5MM



TE Part # 925366-3  
MOD 4 REC.HSG 1X03P


Also in the Series | AMPMODU Headers




Connector Caps & Covers(1)



Connector Contacts(64)



Connector Hardware(2)



PCB Headers & Receptacles(3202)



Wire-to-Board Connector Assemblies & Housings(5)


Customers Also Bought



TE Part #T4141412041-000  
M12,REAR MOUNTING,FEMALE,B CODE,4P



TE Part #T4171110005-001  
M12,REAR MOUNTING,FEMALE,A,5P, 0.2M WIRE



TE Part #5747844-4  
09 MSFL RCPT RA 318 (IN,FM,BL)



TE Part #TAA755A5501-002  
M12A5-MS-FS-PUR-1.0M



TE Part #406732-2  
MJ,10MM,8P,SHLD,NO HSG POST,SN

TE Part #826632-8  
8P AMPMODU II PIN HDR.

TE Part #354071-E  
SMCB 20 F AB VV 7-23 CL \* H007 137 E002

TE Part #5-1393788-3  
Small Signal Relay, Axicom P2 Standard

Documents

Product Drawings

3P AMPMODU II STIFT LEI

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_826647-3\_P.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_826647-3\_P.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_826647-3\_P.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English