




Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Tin**

Wire Contact Termination Area Plating Material: **Pre-Tin**

Operating Voltage: **600 VAC**

Contact Retention Within Housing: **With**

Features

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Mating Square Post Dimension	1.14 mm[.045 in]
Wire Contact Termination Area Plating Thickness	2.54 µm[100 µin]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	2.54 µm[100 µin]
Contact Orientation	Straight
Contact Type	Socket
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	With
Contact Base Material	Brass
Contact Current Rating (Max)	9 A

Termination Features

--	--



Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Compatible Insulation Diameter Range	1.5 – 3.1 mm[.059 – .122 in]
Wire Size	.3 – .82 mm²

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Reel
------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2151096-1 OCEAN-2.0-APPLICATOR-S-062F125F-RSM	 TE Part # 2238020-1 VAL-U-LOK PIN BR TN 22-18 LP	 TE Part # 2238021-1 VAL-U-LOK SKT BR SN 22-18 LP	 TE Part # 91388-2 PRO-CRIMPER DIE(ONLY)
 TE Part # 2151096-2 OCEAN-2.0-APPLICATOR-S-062F125FA-RSA	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 5-2151096-1 OCEAN-2.0-APPLICATOR-S-062F125F-RSM	 TE Part # 5-2151096-2 OCEAN-2.0-APPLICATOR-S-062F125FA-RSA
 TE Part # 7-2151096-7 OCEAN_2.0_SPARE_PART_KIT-062F125F	 TE Part # 7-2836879-7 OC-062F125F-752-CRIMPTOOLINGKIT		

Customers Also Bought

 TE Part #WP-4P WEDGE LOCK, 4P, REC, ORG, DTP	 TE Part #1-480345-0 08P CMNL CAP HSG F/H NATL	 TE Part #1-480425-0 04P CMNL PLUG HSG P/M NATL	 TE Part #1586019-8 8P RCPT VAL-U-LOK V0
---	--	---	--





TE Part #1-480283-0
08P CMNL PLUG HSG M/M NATL




TE Part #66100-4
III+ SKT,18-16,30AU/FL,STRIP



TE Part #350538-1
UMNL PIN 20-14 .0126 PTPBR



TE Part #DTP04-4P-L012
REC, 4P, GRY, N, FLANGE



TE Part #1-1586765-4
14P RCPT VAL-U-LOK GW



TE Part #1987281-2
HVT SOCKET CONTACT 4.0 sq mm, ASSY

Documents

Product Drawings

VAL-U-LOK SKT BR SN 18-22AWG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_794956-5_G_c-794956-5-g.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_794956-5_G_c-794956-5-g.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_794956-5_G_c-794956-5-g.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English