


PPCEGG0003CLL Datasheet

Product Name // 3 Contacts Fixed Socket 00 Series Push Pull Connector

 [View Product Page](#)

* Representative product image only





// Product Description:	
3 Contacts Fixed Socket 00 Series Push Pull Connector - M7x0.5mm Thread - Nut installation 1Nm - ROHS compliance - Available in Straight Plug version - IP50 rated	- Temp:-50 C to +200 C - Solder Terminals - Durability >4500 cycles - Operating humidity up to 95% - Salt Spray Corrosion Test>144h - High packing density for space savings on panel mounts

// General Information:	
Product Display Title:	00 Series Fixed Socket Push Pull Connector
Product Family:	Circular Automation Connectors
Product Series:	Push Pull Connectors X Series
Contact Pin Material:	Phosphor bronze gold plated 3u"
Coupling Nut Retention Force:	1Nm
Current Max:	3A
Diameter Over Coupling Ring Mm:	8mm
Durability:	>4500 cycles
Fixing Nut Material:	Nickel Plated brass
Function:	Fixed Socket Push Pull Connector
Insulator:	PPS
Ip Rating:	IP50
Max Contact Accomodation Awg:	30AWG
Max Contact Accomodation Mm2:	0.05mm2
Max Operating Temperature:	+200°C
Min Operating Temperature:	-50°C
Max Panel Thickness:	5.5mm
Number Of Contacts:	3 Contacts
Operating Humidity:	0.95
Panel Cut Out:	7.10mmx6.40mm
Pin Pin Terminal Voltage:	800V
Pin Shell Terminal Voltage:	950V
Push Pull Connector Series:	00 Series
Rohs Compliant:	Yes
Salt Spray Corrosion Test:	48h
Shielding Efficiency Min:	75dB
Shielding Efficiency Max:	40dB
Shock Resistance:	100g
Terminal Diameter:	0.5mm
Thread Size:	M7x0.5mm
Vibration Resistance Min:	10Hz
Vibration Resistance Max:	2000Hz

// Product PDF Links

 Push-Pull Connector X Series...

// Product 3D CAD Model Links

 PPCEGG0003CLL3D CAD Model