




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **10**

Number of Rows: **2**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stackable	Yes
PCB Mount Orientation	Vertical
Number of Positions	10
Number of Rows	2
Board-to-Board Configuration	Parallel

Body Features

Connector Profile	Standard
Primary Product Color	Black

Contact Features



Contact Protection Type	Closed Entry Housing
Mating Square Post Dimension	.64 mm[.025 in]
PCB Contact Termination Area Plating Material Thickness	2.5 µm[98.42 µin]
Contact Layout	Inline
Mating Pin Diameter	.63 mm[.025 in]
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.762 µm[30 µin]
Contact Type	Socket
Contact Current Rating (Max)	3 A

Termination Features

Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Rectangular Termination Post & Tail Width	.7 mm[.027 in]
Termination Method to PCB	Surface Mount

Mechanical Attachment

Mating Alignment	Without
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Mating Entry Location	Bottom & Top
Centerline (Pitch)	2.54 mm[.1 in]
Housing Material	LCP (Liquid Crystal Polymer)

Dimensions

Connector Height	6.2 mm[.244 in]
Row-to-Row Spacing	2.54 mm[.1 in]
Stack Height	9 mm[.354 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]

Usage Conditions

--	--



Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Solder Process Feature	Board Standoff
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	600
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1241050-5
2x5P MOD II BREAK AWAY HDR,SMD,
BLISTER



TE Part # 826632-5
5P AMPMODU II PIN HDR



TE Part # 826656-5
5P AMPMODU II STIFT LEI




TE Part # 826634-5
05P MODU 2 PIN HDR.



TE Part # 826658-5
5P AMPMODU II STIFT LEI



TE Part # 826662-5
5P AMPMODU II STIFT LEI



TE Part # 966269-5
2x5P MOD II BREAK AWAY HDR,SMD,
TUBE PKG



TE Part # 826664-5
5P MOD2 STIFT LEI



TE Part # 829394-5
2X5P MOD II UNSHRD HDR, ST, 0.8 AU



TE Part # 215447-5
2X 5P MOD2 STIFTLEI



TE Part # 966709-5
2X5P MODU II BREAK AWAY HEADER,
SMD




TE Part # 828132-5
5P MOD2 STIFT LEI



TE Part # 826659-5
MOD2 HEADER DR 5P

Also in the Series | AMPMODU HV-100/HV-190



PCB Headers & Receptacles(333)

Customers Also Bought



TE Part #5745886-1
25 RCPT SP/MS CNUT



TE Part #5747190-1
09 RCPT SP/MS CNUT



TE Part #5222006-1
RECEPTACLE,PRESS FIT,COML BNC



TE Part #2-292173-5
CT BOX HDR H SMT 5P O/TAPE BLA



TE Part #969973-2
2x2P HV100 REC. CON, SMD, GOLD, BLISTER



TE Part #1-1614959-0
CPF0805 1M3 0.1% 25PPM 1K RL



TE Part #7-1625868-7
RP 2A 0.25W 33R2 0.1% 25PPM 1K RL



TE Part #2825206-1
VAL-U-LOK PIN HCS SN 16AWG



TE Part #60-0251-011-P00
CONTACT SOCKET 1 MM

Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_969973-5_E.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_969973-5_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_969973-5_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.