




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **509 – 1900 CMA**

Mating Tab Width: **4.75 mm [.187 in]**

Features

Product Type Features

Terminal Features	Wire Stop
Insertion Force	Normal

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Body Features

Insulation Material	Nylon
---------------------	-------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	Compression
Barrel Type	Closed

Termination Features



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Terminal Material Thickness	.41 mm[.016 in]
Product Length	20.36 mm[.8 in]
Compatible Insulation Diameter Range	3.43 mm[.135 in]
Wire Size	509 – 1900 CMA

Usage Conditions

Insulation Option	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, RU (UL Component Program)
---	--------------------------------

Packaging Features

Packaging Quantity	3500
Packaging Method	Reel

Other

Barrel Color	Red
--------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2836324-2
OCEAN_2.0_Applicator-S-198SP243SP-SSA

KIT
REPRESENTATION ONLY

TE Part # 7-2836324-7
OCEAN_2.0_SPARE_PART_KIT-198SP243SP

Also in the Series | FASTON 187

Crimp Terminal Housings(41)

Insertion & Extraction Tools(1)

Joints & Splices(1)




PCB Terminals(42)

Quick Disconnects(208)

Splices(1)

Customers Also Bought



 TE Part #640919-1 RECEPT,PIDG FASTON 16-14 187	 TE Part #DTM04-3P-E004 REC, 3P, BLK, N	 TE Part #1609117-8 10EGS1-2=F8241	 TE Part #DRC10-24PA HDR, 24P, BLK, ST, SDR CUP, SN/NI /CU, A
 TE Part #5103311-1 A/L LOW PRO HDR 10P RA BLACK	 TE Part #54753-1 TERMINAL R 90 DEG PG 6 10	 TE Part #5-103168-9 22 MODII HDR DRST SHRD .100CL	 TE Part #454276-1 FLOATING SHEAR
 TE Part #324047 TERM, TERMINYL, RT, 6 AWG, 1/4	 TE Part #453910-1 CRIMPER, WIRE-.180 WIDE F		

Documents

Product Drawings
RECEPT,PIDG FASTON 22-18 187

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_640916-1_M.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_640916-1_M.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_640916-1_M.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



PIDG_FASTON

English

Ultra-Fast and Ultra Fast Plus

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English