

Applicable standard									
Rating	Operating temperature range	-55°C to + 85°C (Note 1)		Storage temperature range	-10°C to + 60°C (Note 3)				
	Operating humidity range	20% to 80% (Note 2)		Storage humidity range	40% to 70% (Note 3)				
	Voltage	1000V AC/DC		Applicable connector	DF22-*(D) S-7. 92C (28) DF22#-*(D) S-7. 92C				
	Current(* 1)	AWG14 : 20A AWG16 : 15A			Applicable cable UL1430/UL1007 AWG14, 16				
	Rated voltage	Rated current		Overvoltage category	IP-Protection method				
UL	AC 600V	AWG14:26A/AWG16:21A (At ambient temp. 25°C)		—	—				
C-UL	AC 600V	See above(*1) (Temp. rise up 30°C MAX)		—	—				
TÜV	AC 600V	See above(*1)		II	IPOO				
Specifications									
Item	Test method		Requirements		QT AT				
Construction									
General examination	Visually and by measuring instrument.		According to drawing.		X X				
Marking	Confirmed visually.				X X				
Electric characteristics									
Contact resistance	20mV MAX, 1mA (DC OR 1000 Hz).		5mΩ MAX.		X —				
Mechanical characteristics									
Mechanical operation	50 times insertions and extractions.		① Contact resistance: 10 mΩ MAX. ② No damage, crack or looseness of parts.		X —				
Vibration	Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 2 h, for 3 directions.		① No electrical discontinuity of 1 μs. ② No damage, crack or looseness of parts.		X —				
Shock	490 m/s <sup>2</sup> duration of pulse 11 ms at 3 times for 3 directions.				X —				
Environmental characteristics									
Rapid change of temperature	Temperature -55 → 5 to 35 → +85 → 5 to 35 °C Time 30 → 5 max → 30 → 5 max min Under 5 cycles.		① Contact resistance: 10 mΩ MAX. ② No damage, crack or looseness of parts.		X —				
Damp heat (Steady state)	Exposed at 40 ± 2 °C, 90 to 95 %, 96 h.		① Contact resistance: 10 mΩ MAX. ② No damage, crack or looseness of parts.		X —				
Remarks									
Note 1: Include the temperature rising by current. Note 2: No condensing Note 3: Apply to the condition of long term storage for unused products before harness assembly. After harness assembly, operation temperature and humidity range is applied for interim storage during transportation.									
Count	Description of revisions		Designed	Checked	Date				
△									
Unless otherwise specified, refer to IEC 60512.				Approved	HS. OKAWA				
				Checked	SZ. ONO				
				Designed	TS. KUMAZAWA				
				Drawn	TS. KUMAZAWA				
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			Drawing no.		ELC-388481-00-00				
HRS	Specification sheet		Part no.	DF22-1416PCA					
	Hirose electric co., ltd.		Code no.	CL680-1192-0-00	△ 1/1				