




Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**
PCB Thickness (Recommended): **1.57 mm [.062 in]**
Mating Tab Width: **6.35 mm [.25 in]**
Mating Tab Thickness: **.8 mm [.031 in]**
PCB Hole Diameter: **1.4 mm [.055 in]**

Features

Configuration Features

Connection Capacity	Single
---------------------	--------

Contact Features

PCB Contact Termination Area Plating Material Thickness	3.81 μm[150 μin]
Contact Underplating Material Thickness	1.27 μm[50 μin]
Contact Mating Area Plating Material Thickness	3.81 μm[150 μin]
PCB Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.8 mm[.031 in]
Terminal Plating Material	Tin
Terminal Size	6.35
Terminal Orientation	Straight

Termination Features

Termination Method to PCB	Through Hole - Solder
Product Terminates To	Printed Circuit Board



Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Extension Below Board	3.18 mm[.125 in]
Terminal Material Thickness	.8 mm[.031 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
PCB Hole Diameter	1.4 mm[.055 in]
Profile Height from PCB	23.8 mm[.948 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-30 – 110 °C[-22 – 230 °F]

Packaging Features

Packaging Quantity	10000
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1217332-1 187 FASTON,PCB TAB,TCBR	 TE Part # 63860-1 187 FASTON TAB TPBR	 TE Part # 62221-1 187 FASTON TAB TPBR	 TE Part # 1217136-1 250 FASTON,PCB TAB,TNBR
 TE Part # 1217061-1 187 FASTON,FLAG,TAB,TNBR	 TE Part # 63952-1 250 FASTON TAB TPBR	 TE Part # 63860-2 187 FASTON TAB TPBR	 TE Part # CAT-P100 Pin Insertion Machine P100
 TE Part # CAT-P280 P280 PIN INSERTION MACHINE	 TE Part # CAT-P300 Pin Insertion Machine P300	 TE Part # CAT-P360 P360 Pin Insertion Machine	 TE Part # CAT-P550 Pin Insertion Machine P550
 TE Part # 1217136-3 250 FASTON,PCB TAB,TNBR	 TE Part # 2410420-3 EP PIN INSERTION MACHINE	 TE Part # 2688850-1 P300-C 4 HEAD	

Also in the Series | FASTON 250



Compression Connectors(4)



Crimp Terminal Housings(132)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(134)



Quick Disconnects(426)



Splices(4)

Customers Also Bought



TE Part #T4111501041-000
M12,MALE,STRAIGHT,D CODE,4P,
PG7,GOLD



TE Part #934922-000
RMW-75/22-1200/ADH-0



TE Part #1-1419104-7
T9AS1D22-12



TE Part #5-1437567-3
MPG206R=(MSPG) SW PUSHBUTTON



TE Part #928343-4
STD TIMER GEH 4P




TE Part #293009-1
4 POS. FASTIN-FASTON CONN. TAB
HOUSING R



TE Part #964204-1
STD-POW-TIM KONTAKT



TE Part #928343-2
STD-TIM GEH 2P



TE Part #927742-6
6 POS FASTIN/ON HOUSING PANEL
MOUNT



TE Part #33220
TERMINAL,SOLIS R 12-10 3/8

Documents



Product Drawings

250 FASTON TAB TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63949-1_K_c-63949-1-k.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_63949-1_K_c-63949-1-k.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63949-1_K_c-63949-1-k.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTON PCB Tabs and Receptacles

English

PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS

English

Product Specifications

Application Specification

English