

VIP-3/PT/FLK40 - Termination board

2903793

<https://www.phoenixcontact.com/us/products/2903793>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with push-in connection and flat-ribbon cable connector, for mounting on NS 35 DIN rails, with pin strip plus short and long locking latches for socket strips, 40-pos.

Commercial data

Item number	2903793
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C423
Product key	CK2121
Catalog page	Page 551 (C-5-2019)
GTIN	4046356796675
Weight per piece (including packing)	197.2 g
Weight per piece (excluding packing)	197.2 g
Customs tariff number	85366990
Country of origin	US

VIP-3/PT/FLK40 - Termination board

2903793

<https://www.phoenixcontact.com/us/products/2903793>



Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	40
No. of channels	2
	4
	6
	8
	16
	32

Data management status

Article revision	04
------------------	----

Insulation characteristics

Oversupply category	II
Pollution degree	2

Electrical properties

Max. permissible operating voltage	25 V AC
	60 V DC
Max. current carrying capacity per branch	1 A
Rated surge voltage	0.6 kV

Supported controller ALLEN-BRADLEY SLC 500

Suitable I/O card	1746 OB 32
	1746 OV 32
	1746 IB 32
	1746 IV 32

Connection data

Field level

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross section AWG	26 ... 14

Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	40
Pitch	2.54 mm

VIP-3/PT/FLK40 - Termination board

2903793

<https://www.phoenixcontact.com/us/products/2903793>



Signaling

Status display	no
Status display present	No

Dimensions

Item dimensions	
Width	77.4 mm
Height	75.8 mm
Depth	63 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Housing insulation material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

VIP-3/PT/FLK40 - Termination board


2903793

<https://www.phoenixcontact.com/us/products/2903793>



Drawings

Circuit diagram



VIP-3/PT/FLK40 - Termination board

2903793

<https://www.phoenixcontact.com/us/products/2903793>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2903793>

	CSA	Approval ID: 2122203		
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	26 - 14	-

	cUL Recognized	Approval ID: E238705		
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	26 - 14	-

	UL Recognized	Approval ID: E238705		
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	26 - 14	-

	CSAus	Approval ID: 2122203		
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	26 - 14	-

cULus Recognized

cCSAus

VIP-3/PT/FLK40 - Termination board

2903793

<https://www.phoenixcontact.com/us/products/2903793>



Classifications

ECLASS

ECLASS-11.0	27141152
ECLASS-13.0	27141152
ECLASS-12.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VIP-3/PT/FLK40 - Termination board

2903793

<https://www.phoenixcontact.com/us/products/2903793>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com