




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **1.31 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Connection Capacity	Single
Compatible With Wire & Cable Type	Discrete Wire

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Body Features

Insulation Material	Nylon
---------------------	-------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Flag
Contact Base Material	Brass



Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Closed

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Terminal Material Thickness	.41 mm[.016 in]
Product Length	16.05 mm[.632 in]
Compatible Insulation Diameter Range	4.7 mm[.185 in]
Wire Size	1.31 – 2.08 mm²

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
Compatible With Approved Standards Products	CSA LR7189, UL E66717
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	2100
Packaging Method	Strip/Reel

Other

Barrel Color	Black
--------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2024 (241)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 90391-3
DIES ULTRA-FAST FASTON 16-14 DIE SET

TE Part # 2150253-2
OCEAN_2.0_APPLICATOR-E-237D-REA

TE Part # 7-2150253-7
OCEAN_2.0_SPARE_PART_KIT-237D

Also in the Series | Ultra-Fast 250

Automotive Connector Caps & Covers (1)

Automotive Housings(5)

Quick Disconnects(49)

Customers Also Bought





TE Part #TAD14145101-001
M12D4-MS-PUR TYPE C GREEN-0.5M



TE Part #8-1393243-0
RT425005



TE Part #1-2176325-9
CRGP 0402 330R 1%



TE Part #P5407601200-000
PN-507939_PLASTIC DUST CAP, M12



TE Part #1241414-3
AMP MCP 6.3/4.8K, CONTACT, SWS



TE Part #2272162-1
MCON WIRE DRESS, 4P, STRAIGHT




TE Part #5-2297811-1
3POS,HPF 1.2,REC HSG,ASSY,SLD



TE Part #2272164-1
MCON WIRE DRESS, 3P, STRAIGHT



TE Part #L9000024-01
Antenna 1/2 Wave Whip 2.4GHz SMA



TE Part #ANT-DB1-WRT-RPS
Antenna Dome WiFi6 2.4/5.8GHz
RG174 RPS

Documents

Product Drawings

ULTRA-FAST 250 ASY FLAG REC 16-14 TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-520132-2_S.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-520132-2_S.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9-520132-2_S.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Ultra-Fast and Ultra Fast Plus

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English