



Connectors > Connector Accessories > Connector Hardware



Hardware Accessory Function: Latching, Locking & Retention

Connector Hardware Accessory Type: Screw Retainer Kit

Features

Product Type Features

Hardware Accessory Function	Latching, Locking & Retention
Connector Hardware Accessory Type	Screw Retainer Kit

Mechanical Attachment

Thread Size	4-40
-------------	------

Dimensions

Product Feature Length	7.62 mm[.3 in]
------------------------	----------------

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag, Bulk

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)



Candidate List Declared Against: JUNE 2024 (241)  
SVHC > Threshold:  
Pb (.35% in Component Part)

**Article Safe Usage Statements:**  
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 5745189-1  
37 RCPT SP/MS STD




TE Part # 5745136-4  
MALE SCRW RETAINER KT,BULK PKG


Also in the Series | AMPLIMITE HDF



Connector Hardware(3)













Connector Strain Relief(5)



IDC D-Sub Connectors(36)

Customers Also Bought



 <p>TE Part #745230-2 20DF SOCKET CONTACT,PLATED</p>	 <p>TE Part #205202-2 20DF PIN CONTACT,PLATED</p>	 <p>TE Part #205841-3 CPC RECPT ASSEMBLY SIZE 11-8</p>	 <p>TE Part #5745175-2 CABLE CLAMP KIT,SZ 5</p>
 <p>TE Part #5555163-2 MJ,LPF,R/A,6P/4C,PNL STOPS,BU</p>	 <p>TE Part #1-770253-0 UMNLII SOK PTPHBZ LP LF 24-18</p>	 <p>TE Part #1734098-8 Champ050 80p A/P RCPT 25CL PB</p>	 <p>TE Part #CONSMA016-15-G SMA Jack 50 Ohm Panel Mount</p>
 <p>TE Part #284583-1 CAVITY PLUG FOR 64 POS CONNECT</p>	 <p>TE Part #ZPF000000000147772 CTJ720E01B-513</p>		

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_5746881-2\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_5746881-2\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_5746881-2\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English