



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **254 – 642 CMA**

Mating Tab Width: **6.35 mm [.25 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Connection Capacity	Single
Compatible With Wire & Cable Type	Discrete Wire

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------



Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Terminal Material Thickness	.41 mm[.016 in]
Product Length	19.68 mm[.774 in]
Compatible Insulation Diameter Range	1.01 – 1.52 mm[.04 – .06 in]
Wire Size	254 – 642 CMA

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Quantity	12000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2150553-2
OCEAN-2.0-APPLICATOR-E-062F080F-REA

TE Part # 346697-3
250 FASTON,REC.,20-16 AWG,PB

TE Part # 7-2150553-7
OCEAN_2.0_SPARE_PART_KIT-062F080F

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(132)

Insertion & Extraction Tools(6)

Magnet Wire Terminals(1)



PCB Terminals(134)

Quick Disconnects(426)

Splices(4)

Customers Also Bought



 TE Part #HDP26-24-18SN-L017 PLG, 18P, BLK, N, RNG, 8/12/16, S	 TE Part #206512-6 LARGE CABLE CLAMP KIT,BULK PKG	 TE Part #3-6609987-6 15SRBS8=F8222H	 TE Part #1658527-7 622-1641LF FEM SOCKET,LEAD FREE
 TE Part #87227-7 14 MODII HDR DRST UNSHRD .100	 TE Part #53247-2 TERMINAL,PG SPR SPD 12-10 8	 TE Part #1-280050-2 250 FASTON,FLAG,REC.,16-20 AWG, TPBR	 TE Part #61818-1 110 FASTON REC 26-22 AWG BR
 TE Part #640911-2 RECEPT,PIDG FASTON 22-18 205	 TE Part #1878643-6 M5031C		

Documents

Product Drawings

250 FASTON REC 26-22 AWG BR

English

CAD Files

Customer View Model

ENG_CVM_CVM_61202-1_T.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_61202-1_T.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_61202-1_T.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English