




TE Internal #: 925856-2

Pin, Mating Pin Diameter 1.6 mm [.063 in], 15 – 13 AWG Wire Size,
1.5 – 2.5 mm² Wire Size, 3256 – 5178 CMA Wire Size, Crimp Wire
Pins, Tabs & Ferrules

[View on TE.com >](#)

Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules



Crimp Wire Terminal Type: **Pin**

Mating Pin Diameter: **1.6 mm [.063 in]**

Wire Size: **3256 – 5178 CMA**

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
------------------------------------	----------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Contact Features

Crimp Wire Terminal Type	Pin
Mating Pin Diameter	1.6 mm[.063 in]
Barrel Type	Open
Terminal Plating Material	Unplated
Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	3256 – 5178 CMA
Barrel Inside Diameter	.8 mm[.032 in]
Terminal Material Thickness	.25 mm[.01 in]
Overall Product Length	7 mm[.275 in]



Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Quantity	30000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2150189-1
[OCEAN_2.0_APPLICATOR-E-0800-REM](#)



TE Part # 2150189-2
[OCEAN_2.0_APPLICATOR-E-0800-REA](#)



TE Part # 7-2150189-7
[OCEAN_2.0_SPARE_PART_KIT-0800](#)

Customers Also Bought




TE Part #170002-4
[SHUR PLUG 20-14 AWG 0.5 X 11.44 TPBR](#)



TE Part #293388-3
[NECTOR S PLUG HV-4 WHITE](#)



TE Part #925552-1
[AM WIRE PIN 20-17 .013 BR](#)



TE Part #925553-1
[AM WIRE PIN 17-13 .013 BR](#)



TE Part #CH02064001
[VERSAFLEX-1-1/4-0-SP](#)



TE Part #2119582-2
[Crimper, Insulation F Premium](#)



TE Part #4030-006-120
[6G TRIAXIAL MEMS DC ACCELEROMETER](#)



TE Part #1393450-5
[V23542C1052B300=KABELBAUMST 80](#)



TE Part #1740336-1
[MICRO QUADLOK SYSTEM SOCKET CONTACT](#)



TE Part #4-2176611-1
[EP 2W \(SS\) 47R 5%](#)

Documents

Product Drawings

[WIRE PIN 15.5-13.5 AWG .01 BR](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_925856-2_D.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_925856-2_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_925856-2_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.