




Connectors > Contacts > Connector Contacts



Contact Type: **Socket**
Contact Mating Area Plating Material: **Gold**
Wire Contact Termination Area Plating Material: **Gold Flash**
Operating Voltage: **250 VAC**
Compatible With Wire & Cable Type: **Discrete Wire**

Features

Product Type Features

Applied Pressure	High
------------------	------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Termination Resistance	12 mΩ
Insulation Resistance	5000 MΩ
Dielectric Withstanding Voltage (Max)	750 V
Operating Voltage	250 VAC

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
Contact Type	Socket
Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Material	Gold Flash
Contact Base Material	Phosphor Bronze









Contact Current Rating (Max)	3 A
Termination Features	
Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable
Mechanical Attachment	
Wire Insulation Support	With
Dimensions	
Wire Size	236.823 – 789.41 CMA
Usage Conditions	
Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
Operation/Application	
Circuit Application	Power & Signal
Industry Standards	
Compatible With Approved Standards Products	CSA LR7189, UL E28476
Packaging Features	
Packaging Quantity	12500
Packaging Method	Reel
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-87499-7 10 MODIV HSG SR MRKD .100CL	 TE Part # 1-102387-2 64 MODIV HSG COMP DR .100 POL	 TE Part # 87499-7 04 MODIV HSG SR MRKD .100CL	 TE Part # 1-87456-5 20 MODIV HSG COMP DR .100CL
 TE Part # 1-87631-6 20 MODIV HSG DR MRKD .100 POL	 TE Part # 87977-8 20 MODIV HSG DR MRKD .100 POL	 TE Part # 102387-5 24 MODIV HSG COMP DR .100 POL	 TE Part # 102241-6 08 MODIV HSG COMP SR .100 POL
 TE Part # 87977-4 12 MODIV HSG DR MRKD .100 POL	 TE Part # 102387-7 30 MODIV HSG COMP DR .100 POL	 TE Part # 1-87499-0 05 MODIV HSG COMP SR .100CL	 TE Part # 87499-4 02 MODIV HSG COMP SR .100CL
 TE Part # 87456-6 10 MODIV HSG DR MRKD .100CL	 TE Part # 102387-6 26 MODIV HSG COMP DR .100 POL	 TE Part # 102387-9 40 MODIV HSG COMP DR .100 POL	 TE Part # 87456-1 06 MODIV HSG COMP DR .100CL




TE Part # 102387-4
20 MODIV HSG COMP DR .100 POL



TE Part # 102387-2
14 MODIV HSG COMP DR .100 POL




TE Part # 87977-1
06 MODIV HSG DR MRKD .100 POL



TE Part # 1-86177-3
12 MODIV HSG COMP DR .100CL

Also in the Series | AMPMODU IV/V




Backplane Connector Housings(1)



Connector Caps & Covers(15)




Connector Contacts(321)



Connector Hardware(13)



Insertion & Extraction Tools(4)



PCB Headers & Receptacles(931)



Rectangular Connector Housings(5)



Standard Rectangular Connectors(7)




Wire-to-Board Connector Assemblies & Housings(436)

Customers Also Bought



TE Part #1658614-4
09 POS HDF RCPT, AP, LEAD FREE



TE Part #1-5102160-2
A/L UNIV HDR 64P RA




TE Part #7-6609107-2
PS0S0DS6B=C1185




TE Part #102387-1
10 MODIV HSG COMP DR .100 POL





TE Part #640391-1
.062 COMM P&S PIN 24-30 PTPBR




TE Part #205169-1
RECEPT ASSY,50 POSN,AMPLIMITE




TE Part #5053302020
RNF-100-1-2-STK



TE Part #2208338-1
6POS,NANOMQS,REC HSG,CODA



TE Part #745530-1
9 POS COVER KIT



TE Part #7-690618-5
ANVIL, SPLICE TYPE

Documents

Product Drawings

MOD V RECP PLTD 30 AU

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_87809-1_K.3d_igs.zip

English

Customer View Model

ENG_CVM_87809-1_K.3d_stp.zip

English

Customer View Model

ENG_CVM_87809-1_K.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION5_CONT

English

1-1773720-9_AMPMODU_MOD_IV_V_QRG

English

Product Specifications

Application Specification

English

87809-1

Socket Contact, Gold, 250 VAC, Discrete Wire, 26 – 22 AWG Wire Size, .12 – .4 mm² Wire Size, 236.823 – 789.41 CMA Wire Size, Crimp, AMPMODU IV/V

