









SECTION X-X



SECTION Z-Z
INSULATION BARREL




SECTION Y-Y
WIRE BARREL



NOTES:

1. MATERIAL -
PHOSPHOR BRONZE CDA 521
THICKNESS : 0.200/[.008]
TENSILE STRENGTH = 655 ~ 760 N/mm²
PLATING - SEE SHEET 2
2. FOR DIMENSION A,B,C,D,F & G
SEE SHEET 2
3. FOR WIRE SIZE & INSULATION DIA
SEE SHEET 2
4. THIS TERMINAL TO MATE WITH
0.635 / [.025] SQUARE PIN
5. MAX BURR AFTER CUT-OFF
0.025 / [.001]

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex				
mm/[in]		NTS										
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 798766 DRWN: SUAIFR 2023/10/31 CHK'D: SUAIFR 2024/09/19 APPR: MRAMAKRISHNA 2024/09/20				C-GRID III FEMALE CRIMP TERMINAL				
	MM	INCH										
4 PLACES	±		±	INITIAL REVISION: DRWN: NPC 1987/08/27 APPR: MLOMG 2011/07/04				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
3 PLACES	±		± 0.004					SD-90119		PSD	001	M1
2 PLACES	±	0.1	±	PRODUCT CUSTOMER DRAWING								
1 PLACE	±	0.2	±									
0 PLACES	±		±									
ANGULAR TOL ± 0.5 °												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
				A3-SIZE		90119	SEE TABLE		GENERAL MARKET		1 OF 2	

DOCUMENT STATUS	P1	RELEASE DATE	2024/09/20	09:05:31
-----------------	----	--------------	------------	----------

[illegible]