



MATE-N-LOK | Mini-Universal MATE-N-LOK 2

TE Internal #: 794198-1
Housing, Plug, Wire-to-Board / Wire-to-Wire, 12 Position, 4.14 mm [.162 in] Centerline, Mini-Universal MATE-N-LOK 2, Rectangular Power Connectors

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board, Wire-to-Wire**

Number of Positions: **12**

Centerline (Pitch): **4.14 mm [.162 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	12
Number of Rows	2

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features

Multiple Contact Types	Without
Contact Retention Within Housing	Without
Contact Type	Socket



Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	4.14 mm [.162 in]
Housing Color	Natural
Housing Material	Nylon

Dimensions

Row-to-Row Spacing	4.14 mm [.162 in]
--------------------	-------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Rating	Recognized
Compatible With Agency/Standards Products	UL
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	300
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)



Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-794066-1
12P MINI UMNL HDR W/DH AU LF

TE Part # 1-794228-0
MINI UMNL2 PIN 22-18 AWG AU LP

TE Part # 1-770972-0
12P MINI UMNL R/A HDR ASSY LF

TE Part # 1-794066-0
12P MINI UMNL HDR W/DH SN LF




TE Part # 794224-1
MINI UMNL2 PIN 30-26 AWG SN LP

TE Part # 1-770621-0
12P MINI UMNL DBL ROW HDR ASSY

TE Part # 794229-3
MINI UMNL2 SOK 22-18 AWG AU LP

TE Part # 1-770621-1
12P MINI UMNL HDR ASSY AU LF



 TE Part # 1-794222-0 MINI UMNL2 PIN 20-16AWG AU LF	 TE Part # 1-794218-0 MINI UMNL2 PIN 26-22AWG AU LF	 TE Part # 1-794219-0 MINI UNML2 SOK 26-22 AWG AU LF	 TE Part # 1-794223-0 MINI UMNL2 SCKT 20-16AWG 30AU
 TE Part # 794222-1 MINI UMNL2 PIN 20-16AWG SN	 TE Part # 1-794221-0 MINI UMNL2 SOK 22-18AWG AU LF	 TE Part # 794218-1 MINI UMNL2 PIN 26-22 AWG SN	 TE Part # 794220-1 MINI UMNL2 PIN 22-18 AWG SN
 TE Part # 794223-1 MINI UMNL2 SCKT 20-16AWG SN	 TE Part # 794221-1 MINI UMNL2 SOK 22-18 AWG SN	 TE Part # 794219-1 MINI UMNL2 SOK 26-22 AWG SN	 TE Part # 1-794220-0 MINI UMNL2 PIN 22-18 AWG AU

Also in the Series

Mini-Universal MATE-N-LOK 2

 Connector Contacts(34)	 Insertion & Extraction Tools(1)	 Rectangular Power Connectors(45)
---	--	---

Customers Also Bought

 TE Part #5747539-1 KIT,RCPT,15P,HDP-20,SHLD HDWRE	 TE Part #2-1625999-6 HSC100 2R2 5%	 TE Part #794190-1 06P MINI UMNL2 PLUG HSG UL94V0	 TE Part #1-794223-0 MINI UMNL2 SCKT 20-16AWG 30AU
--	---	---	--



Documents

Product Drawings

12P MINI UMNL2 PLUG HSG DBLROW

English

CAD Files

Customer View Model

ENG_CVM_CVM_794198-1_G.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_794198-1_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_794198-1_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English