



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 83700 – 119500 CMA

Stud Size: M10

Features

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	M10
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	24.975 g
----------------	----------

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions



Wire Size	83700 – 119500 CMA
Stud Diameter	10 mm, 10.5 mm[.413 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	49.7 mm[1.953 in]
Barrel Inside Diameter	11.28 mm[.444 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	50
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 150453
TERM, RT, STRAT, SOLIS, HR, 2, M8(5 /16)

TE Part # 36926
TERM,SOLIS R 2/0 5/8

TE Part # 696693-1
TERM,SOLIS FLAG R 2 3/8 NIPL

Customers Also Bought

TE Part #NB07744001
HTAT-24/6-0-SP

TE Part #2-603227-0
CABLE TIE, BLACK, 6" L, 1000/PACK

TE Part #5-963716-1
MQS0,63 Sn tab LL unseal. 0,5-0,75

TE Part #964322-1
SPT A REC 6.3 Contact SRC Sn

TE Part #2820963001
44A0211-22-9

TE Part #710025-5
XCT 50-10

TE Part #185879-2
26W MQS COVER ASSY BLUE

TE Part #4-160256-7
250 FASTON,REC.,17-14 AWG,SPBR

TE Part #1801739-1
18W HYBRID UNSEALED TAB HOUSING BLACK

TE Part #2390077-2
SDE F MQS PIN/SKT 0.75-0.50mm2 DIE SET

Documents

160000

Closed Ring Tongue Terminal, 1/0 AWG, M10 Stud Size, 10 mm / 10.5 mm [.413 in]
Stud Diameter, Closed Barrel, Straight, Tin, Uninsulated



Product Drawings

TERM,SOLIS R 1/0 M10

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_160000_AD.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_160000_AD.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_160000_AD.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English