



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **1**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Color	Clear
-----------------------	-------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)



Housing Features

Housing Material	Nylon
------------------	-------

Dimensions

Product Length	18 mm[.71 in]
----------------	---------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	10000
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 1-480417-0 110 FASTON HSG.,REC.,1 POS, NATRUAL	 TE Part # 1-2133346-0 250 FASTON HSG.,REC.,1 POS, NATRUAL	 TE Part # 1-480418-0 205 FASTON HSG.,REC.,1 POS, NATRUAL	 TE Part # 521053-1 250 FASTON HSG. REC 1P NATURAL
 TE Part # 1-480417-1 110 FASTON HSG.,REC.,1 POS,BLACK	 TE Part # 280233 250 FASTON POST INS.,1 POS, NATRUAL	 TE Part # 925387-2 110 FASTON HSG. REC. 1P CLEAR	 TE Part # 1969186-2 312 FASTON HSG.,REC.,NATRUAL
 TE Part # 1-2133346-1 250 FASTON HSG.,REC.,1 POS,RED	 TE Part # 1-2133346-4 250 FASTON HSG.,REC.,1 POS,BLACK		

Also in the Series | FASTON 110

 Crimp Terminal Housings(13)	 Insertion & Extraction Tools(1)	 PCB Terminals(22)	 Quick Disconnects(168)
--	---	--	---


Customers Also Bought




TE Part #160668-2
110 FASTON FASTON,REC.,20-16 AWG, PTBR



TE Part #5-160432-4
250 FASTON REC 20-16 AWG TPBR



TE Part #280000-6
250 FASTON,REC.,24-17 AWG,TPBR



TE Part #1217566-1
250 FASTON,PCB TAB,TCBR



TE Part #1-2213766-5
AV19 SPM 3A POWER LED GREEN 24V



TE Part #2213767-3
AV19 SPM 3A MOVE RING LED WHITE 24V




TE Part #3-967325-3
2,5MM BU-GEH 2P,GN



TE Part #1564980-1
AMP MCP 1.5K, CONTACT



TE Part #NB09846001
ATUM-19/6-0-50MM



TE Part #2-2227303-4
CAGE ASSEMBLY, SFP, 1.25MM TAIL

Documents

Product Drawings

110 FASTON HSG. REC. 1P CLEAR

German

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_926410-1_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_926410-1_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_926410-1_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.