



Terminals & Splices > Automotive Terminals > MULTILOCK, RECEPTACLE AND TAB



Terminal Type: **Receptacle**

Mating Tab Width: **1 mm [.039 in]**

Mating Tab Thickness: **.64 mm [.025 in]**

Terminal Transmits: **0 – 24 A (Low Power)**

Wire Size: **22 – 20 AWG**

[All MULTILOCK, RECEPTACLE AND TAB \(111\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	Yes
Primary Locking Feature	Clean Body

Body Features

Terminal Seal Type	Single Wire Seal (SWS)
--------------------	------------------------

Contact Features

Contact Size	1mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Gold
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	1 mm[.039 in]
Mating Tab Thickness	.64 mm[.025 in]
Interface Plating	Gold (Au)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire



Dimensions

Compatible Insulation Diameter Range	1.4 – 1.7 mm[.055 – .067 in]
Wire Size	.3 – .5 mm ²
Wire Size Search	20 AWG, 21 AWG, 22 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C[176 °F][185 °F][194 °F][212 °F][221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Packaging Features

Packaging Quantity	5000
Packaging Method	Reel

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2151186-1 OCEAN_2.0_Applicator-S-070F118O-RSM	 TE Part # 2151186-2 OCEAN_2.0_Applicator-S-070F118OA-RSA	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 7-2151186-7 OCEAN_2.0_SPARE_PART_KIT-070F118O
--	---	---	--

Also in the Series | Multilock Connector System

 Automotive Connector Caps & Covers (10)	 Automotive Connector Locks & Position Assurance(3)	 Automotive Housings(445)	 Automotive Terminals(117)
 Connector Seals & Cavity Plugs(2)	 Insertion & Extraction Tools(6)	 Other Automotive Connector Accessories(12)	 PCB Headers & Receptacles(134)

Customers Also Bought

 TE Part #1674312-2 TH/.025 CONNECTOR SYSTEM, HOUSING	 TE Part #344067-1 .250"SPEC.F.TAB.(PLATED)	 TE Part #1565963-2 040III TAB NON SEALED AU	 TE Part #1670326-3 1.5MM SFC,CONTACT
---	---	--	---



TE Part #1612123-1
SQUIB FERRITE

TE Part #1379101-5
COV+LEV MQS 18W 90DEG GREEN

TE Part #1674311-7
0.64 III RCPT 3 Serrations Pre-Tin

TE Part #1801468-1
COVER, ROTATIVE, 3 WAY HP CONNECTOR

TE Part #2367834-1
REC CONN CVR ASSY,84POS,0.5 SERIES,TYPE1

Documents

Product Drawings

040 SEALED REC CONT S FORMING

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_316833-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_316833-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_316833-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

MULTILOCK Connector System

English

Product Specifications

Crimping of 040III Sealed Contact, Tab and Receptacle

Japanese

Application Specification

Japanese

316833-2

Receptacle, Mating Tab Width 1 mm [.039 in], Tab Thickness .64 mm [.025 in], 22 – 20
AWG Wire Size, Multilock Connector System, Automotive Terminals

