




Series
EPXB

SIZE 2 RECEPTACLE CONNECTOR

Issue:
Nov 26,2002

Page
1 / 1




Materials and finishes:

- Shell: aluminium alloy 6061 T651; electrolytic nickel flash over electroless nickel per ISO 4527.
- Jacknut: . Spring: stainless steel AISI 302 (non passivated).
- . All other parts: stainless steel AISI 316 (non passivated).
- Insert retention clip: beryllium copper per ASTM-B-194.
- Grounding spring: beryllium copper per ASTM-B-194; 2,5-7,5 micrometer electrolytic nickel per QQ-N-290.

Notes:

- 1- Connector supplied with polarization device for A, B, C, D, E and F polarization P/N: 617 980 009, uninstalled.
- 2- For side by side mounting, use a 19,50 (.768) min pitch.
- 3- The jacknut has to be locked with resin by the customer.

DIMENSIONS : mm (inch) -



CREATION				
PEN:				
NOM: G.Chevreau				
DATE: Oct. 25, 00				
APPR.: G.Motteau				
	Nov 26.02	Modif of 4-40 threads and shell to prevent front panel mounting	S.Couthon	L.Garcia
	07.16.02	Modification of grounding springs.	L.Garcia	B.VDM
	Issue	Revisions	Name	Approved

AEPXB2HL22N