




MAG-MATE

TE Internal #: 1534684-1
Solder Post, .17 – .25 mm Magnet Wire, 33 – 31 AWG Magnet Wire,
Tin Plating, Length 8.2 mm [.322 in], MAG-MATE, Magnet Wire
Terminals

[View on TE.com >](#)

Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Solder Post**
Magnet Wire Size: **.17 – .25 mm**
Stock Thickness (Magnet Wire Side): **.32 mm [.013 in]**
Terminal Plating Material: **Tin**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire, Solid
------------------------------------	--------------------

Contact Features

Magnet Wire Terminal Type	Solder Post
Terminal Plating Material	Tin
Terminal Orientation	Straight

Dimensions

Terminal Height	4.56 mm[.179 in]
Magnet Wire Size	.17 – .25 mm
Stock Thickness (Magnet Wire Side)	.32 mm[.013 in]
Product Length	8.2 mm[.322 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]

Operation/Application

--



Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Box, Reel, Reel/Carton
------------------	------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # 1217234-1
MAG-MATE TERM 28-31 013TPBR

TE Part # 1742857-1
TAB, PLAIN, 187 MAG-MATE SLIM

TE Part # 1534682-1
MAG-MATE CONTACT .187,WITH SOLDER PIN

TE Part # 1-1534686-7
MAG-MATE CONTACT WITH SOLDER PIN




 TE Part # 1534681-1 MAG-MATE CONTACT.187 WITH SOLDER PIN	 TE Part # 1740829-2 MAG MATE CONTACT WITH SOLDER PIN	 TE Part # 1534686-1 MAG MATE CONT WITH SOLDER PIN	 TE Part # 1534685-1 MAG MATE CONT .300 SOLDER POST
 TE Part # 1-1534686-1 MAG MATE CONT WITH SOLDER PIN	 TE Part # 1-1534685-1 MAG MATE .300 SOLDER POST	 TE Part # 1534680-1 MAG MATE CONT 187, SOLDER PIN	 TE Part # 1534686-7 MAG-MATE CONTACT WITH SOLDER PIN
 TE Part # 1534687-1 MAG-MATE CONTACT WITH SOLDER-PIN	 TE Part # 1740829-1 MAG MATE CONTACT WITH SOLDER PIN	 TE Part # 2-1987224-7 MAGMATE-MQS TERMINAL	

Also in the Series | **MAG-MATE**


 Insertion & Extraction Tools(6)	 Magnet Wire Terminals(337)	 PCB Terminals(1)
--	---	---

Customers Also Bought

 TE Part #1-1318117-3 DYNAMIC D-2100 TAB HSG 3P F/H	 TE Part #179227-1 CRIMP TYPE II REC CONTACT	 TE Part #207360-1 PLUG HSG,3 POSN,METRIC	 TE Part #1-770872-0 02P MINI UMNL HDR ASSY SN
---	--	---	--



TE Part #163087-8
062 SOC.ASS. TYP3+



TE Part #1-180908-0
FF 250 TAB HSG 2P NYLON NAT




TE Part #1-770904-0
MINI UMNL SOK 22-18 AWG AU



TE Part #964269-2
TAB A 1.6x0.6 CONTACT CF SWS Sn



TE Part #794270-1
02P UMNL WIRE SEAL



TE Part #3-1372172-4
CLAMP LEVER

Documents

Product Drawings

MAG MATE CONT .300 SOLDER POST

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1534684-1_C_c-1534684-1-c.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1534684-1_C_c-1534684-1-c.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1534684-1_C_c-1534684-1-c.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Magnet Wire Terminals & Splices

English

CAVITY FOR MAG-MATE CONTACT WITH SOLDER PIN

English

Product Specifications

Application Specification

English

1534684-1

Solder Post, .17 – .25 mm Magnet Wire, 33 – 31 AWG Magnet Wire, Tin Plating,
Length 8.2 mm [.322 in], MAG-MATE, Magnet Wire Terminals

