



Sensors > Force Sensors > Force Sensor Elements



Force Sensor Type: OEM Compression Load Cells
Full Scale Range: 200 lbf
Operating Temperature Range: 0 – 50 °C [32 – 122 °F]

Features

Product Type Features

Force Sensor Type	OEM Compression Load Cells
-------------------	----------------------------

Electrical Characteristics

Supply Voltage Range	5 VDC
Full Scale Range	200 lbf

Usage Conditions

Accuracy	±1 % of FS
Operating Temperature Range	0 – 50 °C[32 – 122 °F]

Other

Zero Shift in CTR	±.05 % of FS
Sensitivity Shift	±.05 % of FS
Force Direction	Compression

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)



Candidate List Declared Against: JAN 2024 (240)
SVHC > Threshold:
2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one (.15% in component part)

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # FX1901-0001-0100-L
FX1901-0001-0100-L



TE Part # FX1901-0001-0025-L
FX1901-0001-0025-L



TE Part # FX1901-0001-0050-L
FX1901-0001-0050-L



TE Part # FX1900-0000-0025-L
25 LBF COMPRESSION LOAD CELL
100MV

Also in the Series | MEAS FX1901



Force Sensor Elements(6)


Customers Also Bought



TE Part #4525-DS5A001DP
PRESS XDCR, ANALOG, PSI RANGE



TE Part #6-1462037-7
IM46GR=IM RELAY 100mW 12V BIS



TE Part #562243-000
82A0111-16-9



TE Part #86-500G-R
500 PSIG RIBBON CABLE MV
PRESSURE SENSOR




TE Part #1-201046-2
SERIES "M" MIN RECT GUIDE PIN



TE Part #5-2213767-1
AV19 DPM 3A MOVE RING LED
YELLOW 24V



TE Part #4030-002-120
2G TRIAXIAL MEMS DC
ACCELEROMETER



TE Part #293770-000
381A301-51/164-0



TE Part #2132415-4
EP2.5 Shrouded HDR ASSY 4P VERT w
/o boss

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_FX1901-0001-0200-L_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_FX1901-0001-0200-L_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_FX1901-0001-0200-L_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FX19

English