



AMP Mini CT

TE Internal #: 292215-2  
Connector Assembly, Plug to Plug Relay Header, Wire-to-Panel, 2  
Position, 1.5 mm [.059 in] Centerline, 1 Row, White, Mating  
Retention, AMP Mini CT

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Connector Assembly**  
Connector & Housing Type: **Plug to Plug Relay Header**  
Connector System: **Wire-to-Panel**  
Number of Positions: **2**  
Centerline (Pitch): **1.5 mm [ .059 in ]**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Plug to Plug Relay Header
Connector System	Wire-to-Panel
Sealable	No

Configuration Features

Number of Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	50 VAC
-------------------	--------

Body Features

Primary Product Color	White
-----------------------	-------

Contact Features

Contact Retention Within Housing	Without
----------------------------------	---------



Contact Type	Pin
Contact Base Material	Brass
Contact Current Rating (Max)	2 A

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	With
Panel Mount Feature Type	Latches
Mating Retention Type	Locking Latch
Mating Retention	With
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Nylon 66
Centerline (Pitch)	1.5 mm[.059 in]

Dimensions

Connector Length	11.1 mm[.437 in]
Panel Thickness (Recommended)	.81 – 1.6 mm[.032 – .063 in]
Connector Height	11.8 mm[.464 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	UL Recognized
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	600
Packaging Method	Bag & Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------




EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 2-179694-2  
2MM CT MT REC ASSY 2P GRAY




TE Part # CAT-AM7053-H8172  
Mini Common Termination (CT) Housings




TE Part # CAT-AM7053-C7671  
Mini Common Termination Contacts




TE Part # 353293-2  
MINI CT MT REC ASSY 2P GRAY



TE Part # 1-353293-3  
MINI CT MT REC ASSY 13P GRAY



TE Part # 5-353293-2  
MINI CT MT REC ASSY 2P BLUE



TE Part # 2405870-1  
CT 2P 300MM CABLE ASSEMBLY 6-353908-2

Also in the Series | AMP Mini CT



Connector Contacts(4)



Connector Hardware(10)



PCB Headers & Receptacles(332)



Wire-to-Board Connector Assemblies & Housings(172)

Customers Also Bought



TE Part #1612257-7  
REC ASSY 7P ,MINI CT DC DRAWER



TE Part #292215-9  
MINI CT SGL RELAY 9P NAT



TE Part #2-353293-4  
1.5MM CT MT REC ASS'Y 4P BLACK



TE Part #2-353293-3  
1.5MM CT MT REC ASS'Y 3P BLACK




TE Part #3-353293-3  
1.5MM CT MT REC ASSY 13P BLACK



TE Part #2-353293-9  
1.5MM CT MT REC ASS'Y 9P BLACK



TE Part #3-353293-2  
1.5MM CT MT REC ASSY 12P BLACK



TE Part #8-292112-2  
MT REC ASSY (#26,28)



TE Part #8-292155-4  
SGL HDR PANEL MOUNT ASSY

Documents

Product Drawings

MINI CT SGL RELAY 2P NAT

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_292215-2\_B.2d\_dxf.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_292215-2\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_292215-2\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Workmanship Specification](#)

English