



Connectors > Rectangular Connectors > Rectangular Contact Inserts



Rectangular Connector Insert Type: **Contact Insert**
Contact Type: **Socket**
Pole Configuration: **24**
Termination Method to Wire & Cable: **Screw Terminal**
Number of Positions: **24**

Features

Product Type Features

Rectangular Connector Insert Type	Contact Insert
Sealable	No

Configuration Features

Number of Positions	24
---------------------	----

Contact Features

Contact Type	Socket
Pole Configuration	24

Termination Features

Termination Method to Wire & Cable	Screw Terminal
------------------------------------	----------------

Dimensions

Wire Size	.5 – 2.5 mm ²
-----------	--------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------



EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # T1510482000-000 H48B-AD-LB	 TE Part # T1610482140-000 H48B-SGR-LB-M40	 TE Part # T2040482101-000 HE-024-M 25-48	 TE Part # T1610482129-000 H48B-SGR-LB-PG29
 TE Part # T1610482132-000 H48B-SGR-LB-M32	 TE Part # T1500482000-000 H48B-AG-LB	 TE Part # T1610482136-000 H48B-SGR-LB-PG36	 TE Part # T1610482142-000 H48B-SGR-LB-PG42



TE Part # T1610482150-000
H48B-SGR-LB-M50

TE Part # T1610482229-000
H48B-SGR-LB-2PG29

TE Part # T1610482232-000
H48B-SGR-LB-2M32

TE Part # T1610482236-000
H48B-SGR-LB-2PG36

TE Part # T1610482240-000
H48B-SGR-LB-2M40

TE Part # T1620480129-000
H48B-SDR-LB-PG29

TE Part # T1620480132-000
H48B-SDR-LB-M32

TE Part # T1620480136-000
H48B-SDR-LB-PG36

TE Part # T1620480140-000
H48B-SDR-LB-M40

TE Part # T1620480142-000
H48B-SDR-LB-PG42

TE Part # T1620480150-000
H48B-SDR-LB-M50

TE Part # T1620480229-000
H48B-SDR-LB-2PG29

Also in the Series | **HDC HE**

Connector Contacts(32)

Rectangular Contact Inserts(127)


Customers Also Bought

TE Part #T1410322000-000
H32B-AG

TE Part #T2010162101-000
HA-016-M

TE Part #T1410242000-000
H24B-AG

TE Part #T2040242201-000
HE-024-F



Documents

Product Drawings

HE-024-F 25-48

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T2040482201-000_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T2040482201-000_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T2040482201-000_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Product Specifications



Application Specification

English

Application Specification

Agency Approvals

Agency Approval Document

English