




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.03 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Terminal Orientation: **Straight**

Features

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Barrel Type	Open

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Terminal Material Thickness	.32 mm[.013 in]
Compatible Insulation Diameter Range	2.3 – 3.3 mm[.089 – .129 in]
Wire Size	.51 – 1.03 mm²

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------



Packaging Features

Packaging Quantity	8000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 160860-3
6,35 FASTIN-FASTON RECEP


TE Part # 160860-2
FF 250 REC 0.5-1.0MM2 TPBR

TE Part # 160860-4
FF 250 REC 0.5-1.0MM2 TPPB


TE Part # 160928-2
FF 250 REC 0.5-1.0MM2 TPBR




TE Part # 160928-4
FF 250 REC 0.5-1.0MM2 TPPB



TE Part # 626094-1
TERMINAL, .250 FASTIN-ON REC




TE Part # 626095-2
FASTIN-ON .250 REC 1.0-2.5 MM2 TPBR



TE Part # 626095-4
.250 SERIES FASTIN



TE Part # 880675-2
FF 250 REC 0.50-1.00 MM2 0.32X19.3 TPBR



TE Part # 880675-3
.250 FASTIN-ON REC.

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(210)



Insertion & Extraction Tools(2)




PCB Terminals(2)



Quick Disconnects(251)

Customers Also Bought



TE Part #880646-6
POSITIVE LOCK REC.



TE Part #444020-1
Timer Connector Housing




TE Part #964304-1
TIMER, RECEPTACLE AND TAB



TE Part #1241404-3
AMP MCP 6.3/4.8K, CONTACT



TE Part #881624-2
187 FASTON REC 17-14 AWG TPBR



TE Part #350566-3
MINI AMP-IN 22-18 PTPBR



TE Part #170002-7
TERMINAL GROUP NUMBER



TE Part #E296612001
DSPL-NR1-X-STK



Documents

Product Drawings

FF .250 REC 0.5 /1.0 MM2 0.32X19.3 TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_626094-2_L1_c-626094-2-l1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_626094-2_L1_c-626094-2-l1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_626094-2_L1_c-626094-2-l1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.