



Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: **Header**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Centerline (Pitch): **5 mm [.197 in]**

Number of Rows: **1**

Features

Product Type Features

Header Type	Fully Shrouded
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stacking Configuration	Side Stackable
Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Green
Product Orientation	Right Angle



Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	15 A

Termination Features

Termination Post & Tail Length	3.5 mm[.138 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Housing Material	PA 66
Centerline (Pitch)	5 mm[.197 in]

Dimensions

Wire Size	.05 – 3 mm²
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Identification Marking

Marking Color	White
---------------	-------

Packaging Features

Packaging Quantity	150
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC




Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 796640-4 4 POS 5.0 MM R/A PLUG, TRM BLK	 TE Part # 284040-4 TERMI-BLOK VERTICAL PLUG STACK	 TE Part # 282805-4 TERMI-BLOK PLUG STACKING 4POS.	 TE Part # 284046-4 TERMI-BLOK VERTICAL PLUG STACK
 TE Part # 1546118-4 4POS.5MM VERT.PLUG LH BLCK	 TE Part # 796641-4 4 POS 5.0 MM R/A PLUG, TRM BLK	 TE Part # 1546557-4 4P, SCREWLESS CLIP PLUG, 5.0MM	 TE Part # 1776148-4 4P TERMI-BLOK HDR, HIGH TEMP
 TE Part # 1986341-4 4POS 5.0MM CE R/A HDR, TRM BLK			

Customers Also Bought



TE Part #776180-1
35POS, PIN DIA 1.3, HDR ASSY, 90DEG, COD 1



TE Part #357197-000
202K121-100/86-0




TE Part #DTM06-12SA-E003
PLG, 12P, GRY, N, CAP, A



TE Part #175149-1
UNIVERSAL POWER CONN TAB




TE Part #175151-1
AMP UNIVERSAL POWER REC CONT.



TE Part #359926-000
204W221-25/225-0



TE Part #6609015-5
6EF1F=F7325 S0



TE Part #163683-8
10P.CIS FEMALE CONN



TE Part #1-1776294-2
TSB23012=EUROPA TERM BLK, 8MM



TE Part #ANT-433-CW-RH-SMA
Antenna 1/4 Wave Short 433MHz SMA

Documents

Product Drawings

4POS 5.0MM CE R/A HDR, TRM BLK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_796644-4_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_796644-4_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_796644-4_C.3d_stp.zip

English

Customer View Model

ENG_CVM_796644-4_C1.3d_igs.zip

English



3D PDF

English

Customer View Model

ENG_CVM_796644-4_C1.3d_stp.zip

English

Customer View Model

ENG_CVM_796644-4_C1.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Eurostyle Terminal Blocks Focus Product Stock List

English

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

BUCHANAN PCB TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English